

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494905

Luminaire Tested: **LDA2B108035R35D010 2LBDC1MMS**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P494905  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/12/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108035R35D010 2LBDC1MMS  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1089.8 lumens  
Efficiency: N/A  
Efficacy: 109.0 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P494905

CATALOG NUMBER: LDA2B108035R35D010 2LBDC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P494905

CATALOG NUMBER: LDA2B108035R35D010 2LBDC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100	99	98	96
2	111	107	104	101	109	106	103	100	102	100	98		100	98	96		97	95	94	93
3	107	102	99	96	105	101	98	95	99	96	93		96	94	92		94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81	78	76	75
9	89	82	77	75	88	81	77	74	80	77	74		80	76	74		79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77	74	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1712656
5°	1647536
10°	1492097
15°	1038642
20°	509011
25°	189874
30°	83402
35°	40534
40°	18548
45°	10047
50°	4912
55°	1376
60°	493
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P494905

CATALOG NUMBER: LDA2B108035R35D010 2LBDC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	307.4	28.2
10°-20°	538.8	49.4
20°-30°	183.6	16.8
30°-40°	45.7	4.2
40°-50°	11.8	1.1
50°-60°	2.2	0.2
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1029.8	94.5
0°-40°	1075.4	98.7
0°-60°	1089.3	100.0
0°-90°	1089.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1089.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3471	
5°	3327	307
15°	2034	539
25°	349	184
35°	67	46
45°	14	12
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494905

CATALOG NUMBER: LDA2B108035R35D010 2LBDC1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3471.4
1°	3464.5
2°	3437.8
3°	3412.1
4°	3371.0
5°	3326.7
6°	3283.4
7°	3242.8
8°	3155.2
9°	3070.3
10°	2978.4
11°	2827.8
12°	2664.3
13°	2453.9
14°	2258.9
15°	2033.5
16°	1813.4
17°	1584.3
18°	1370.1
19°	1153.2
20°	969.5
21°	794.3
22.5°	582.8
23°	523.5
24°	427.3
25°	348.8
26°	288.4
27°	240.9
28°	203.0
29°	171.5
30°	146.4
32.5°	99.4
35°	67.3
37.5°	45.4
40°	28.8
42.5°	19.8
45°	14.4
47.5°	10.1
50°	6.4
52.5°	3.7
55°	1.6
57.5°	1.1
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P494905

CATALOG NUMBER: LDA2B108035R35D010 2LBDC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)