

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494945

Luminaire Tested: **LDA2B108035R45D010 2LBDLC1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494945
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108035R45D010 2LBDLC1MB
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1104.1 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494945

CATALOG NUMBER: LDA2B108035R45D010 2LBDLC1MB

Luminous Intensity Polar Plot





TEST NUMBER: P494945

CATALOG NUMBER: LDA2B108035R45D010 2LBDLC1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1094227
5°	1070128
10°	992878
15°	846696
20°	637432
25°	384321
30°	185319
35°	84019
40°	38642
45°	19955
50°	10515
55°	3957
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P494945

CATALOG NUMBER: LDA2B108035R45D010 2LBDLC1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.9	18.2
10°-20°	452.7	41.0
20°-30°	323.4	29.3
30°-40°	97.0	8.8
40°-50°	24.1	2.2
50°-60°	5.0	0.5
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	977.0	88.5
0°-40°	1074.0	97.3
0°-60°	1103.1	99.9
0°-90°	1104.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1104.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2218	
5°	2161	201
15°	1658	453
25°	706	323
35°	140	97
45°	29	24
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494945

CATALOG NUMBER: LDA2B108035R45D010 2LBDLC1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2217.9
1°	2221.9
2°	2216.8
3°	2197.9
4°	2184.2
5°	2160.8
6°	2137.3
7°	2112.2
8°	2071.0
9°	2032.2
10°	1981.9
11°	1931.5
12°	1868.1
13°	1800.1
14°	1736.6
15°	1657.7
16°	1580.6
17°	1493.1
18°	1410.2
19°	1308.5
20°	1214.1
21°	1109.5
22.5°	953.5
23°	900.9
24°	798.6
25°	706.0
26°	613.4
27°	528.8
28°	449.9
29°	385.3
30°	325.3
32.5°	213.8
35°	139.5
37.5°	91.5
40°	60.0
42.5°	40.6
45°	28.6
47.5°	20.6
50°	13.7
52.5°	8.6
55°	4.6
57.5°	2.3
60°	1.1
62.5°	1.1
65°	0.6



TEST NUMBER: P494945

CATALOG NUMBER: LDA2B108035R45D010 2LBDLC1MB

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)