

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494989

Luminaire Tested: **LDA2B108035R65D010 2LBDL1WHH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494989
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108035R65D010 2LBDL1WHH
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 999.8 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494989

CATALOG NUMBER: LDA2B108035R65D010 2LBDL1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P494989

CATALOG NUMBER: LDA2B108035R65D010 2LBDL1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	523112
5°	501288
10°	477377
15°	453713
20°	422067
25°	389656
30°	338051
35°	242540
40°	131770
45°	56306
50°	24177
55°	8688
60°	1579
65°	1284
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P494989

CATALOG NUMBER: LDA2B108035R65D010 2LBDL1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.8	9.5
10°-20°	248.8	24.9
20°-30°	325.3	32.5
30°-40°	247.5	24.8
40°-50°	71.6	7.2
50°-60°	10.7	1.1
60°-70°	0.9	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	668.9	66.9
0°-40°	916.4	91.7
0°-60°	998.7	99.9
0°-90°	999.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	999.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1060	
5°	1012	95
15°	888	249
25°	716	325
35°	403	247
45°	81	72
55°	10	11
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494989

CATALOG NUMBER: LDA2B108035R65D010 2LBDL1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1060.3
1°	1056.5
2°	1050.7
3°	1038.9
4°	1026.1
5°	1012.2
6°	998.9
7°	987.1
8°	975.9
9°	965.7
10°	952.9
11°	941.7
12°	929.9
13°	918.2
14°	905.4
15°	888.3
16°	875.5
17°	860.0
18°	836.5
19°	824.2
20°	803.9
21°	785.7
22.5°	758.0
23°	747.3
24°	730.7
25°	715.8
26°	696.0
27°	674.1
28°	650.1
29°	624.4
30°	593.4
32.5°	508.5
35°	402.7
37.5°	297.0
40°	204.6
42.5°	129.8
45°	80.7
47.5°	50.2
50°	31.5
52.5°	18.7
55°	10.1
57.5°	3.7
60°	1.6
62.5°	1.1
65°	1.1



TEST NUMBER: P494989

CATALOG NUMBER: LDA2B108035R65D010 2LBDL1WHH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)