

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224475

Luminaire Tested: **LD2B20D010 EU2B20FL409050 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224475
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL409050 2LBDL*WH
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1569.9 lumens
Efficiency: N/A
Efficacy: 75.1 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224475

CATALOG NUMBER: LD2B20D010 EU2B20FL409050 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P224475

CATALOG NUMBER: LD2B20D010 EU2B20FL409050 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87	87	87	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	75	75	75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72	72	72	72
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1448480
5°	1393706
10°	1226730
15°	963547
20°	655117
25°	382556
30°	194830
35°	92161
40°	40249
45°	17420
50°	8376
55°	5403
60°	3099
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224475

CATALOG NUMBER: LD2B20D010 EU2B20FL409050 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	327.4	20.9
10°-20°	653.4	41.6
20°-30°	419.4	26.7
30°-40°	133.1	8.5
40°-50°	28.4	1.8
50°-60°	7.3	0.5
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1400.2	89.2
0°-40°	1533.2	97.7
0°-60°	1568.9	99.9
0°-90°	1569.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1569.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3740	
5°	3584	327
15°	2403	653
25°	895	419
35°	195	133
45°	32	28
55°	8	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224475

CATALOG NUMBER: LD2B20D010 EU2B20FL409050 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3739.5
2.5°	3703.7
5°	3584.4
7.5°	3389.4
10°	3118.9
12.5°	2788.7
15°	2402.8
17.5°	1991.1
20°	1589.3
22.5°	1213.4
25°	895.1
27.5°	638.5
30°	435.6
32.5°	292.4
35°	194.9
37.5°	129.3
40°	79.6
42.5°	49.7
45°	31.8
47.5°	21.9
50°	13.9
52.5°	9.9
55°	8.0
57.5°	6.0
60°	4.0
62.5°	2.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)