

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222426

Luminaire Tested: **LD2B20D010 EU2B20NFL259050 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222426
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20NFL259050 2LBDL*WH
Description: 2000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1526.3 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222426

CATALOG NUMBER: LD2B20D010 EU2B20NFL259050 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P222426

CATALOG NUMBER: LD2B20D010 EU2B20NFL259050 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	95
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	93	92
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	91	90
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	89	88	86
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	87	86	84
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	85	84	82
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84	83	82	80
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	81	80	79
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	79	79	79
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79	79	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3507418
5°	3238451
10°	2192020
15°	745758
20°	273910
25°	145227
30°	74649
35°	34850
40°	11428
45°	5752
50°	2712
55°	1013
60°	1162
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222426

CATALOG NUMBER: LD2B20D010 EU2B20NFL259050 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	708.5	46.4
10°-20°	595.7	39.0
20°-30°	163.5	10.7
30°-40°	47.7	3.1
40°-50°	8.8	0.6
50°-60°	2.0	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1467.6	96.2
0°-40°	1515.3	99.3
0°-60°	1526.1	100.0
0°-90°	1526.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1526.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9055	
5°	8329	708
15°	1860	596
25°	340	163
35°	74	48
45°	10	9
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222426

CATALOG NUMBER: LD2B20D010 EU2B20NFL259050 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	9055.0
1°	9002.3
2°	8909.1
3°	8775.3
4°	8591.9
5°	8328.8
6°	7969.5
7°	7520.0
8°	6971.3
9°	6323.3
10°	5573.1
11°	4750.7
12°	3895.3
13°	3079.0
14°	2382.9
15°	1859.7
17.5°	1049.4
20°	664.5
22.5°	473.6
25°	339.8
27.5°	240.5
30°	166.9
32.5°	117.3
35°	73.7
37.5°	30.1
40°	22.6
42.5°	16.5
45°	10.5
47.5°	6.0
50°	4.5
52.5°	3.0
55°	1.5
57.5°	1.5
60°	1.5
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222426

CATALOG NUMBER: LD2B20D010 EU2B20NFL259050 2LBDL*WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)