

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495111

Luminaire Tested: **LDA2B108040R35D010 2LBD1MW-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P495111
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108040R35D010 2LBD1MW-30DEG TILT
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 790.0 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 3.16 / 0.51 / 1.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P495111

CATALOG NUMBER: LDA2B108040R35D010 2LBD1MW-30DEG TILT

Luminous Intensity Polar Plot





TEST NUMBER: P495111

CATALOG NUMBER: LDA2B108040R35D010 2LBD1MW-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92					90				
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82					80				
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73					71				
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65					63				
5	84	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58					56				
6	77	66	58	53	76	65	58	52	63	57	52	62	56	52	60	55	51					49				
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46					44				
8	67	54	47	42	65	54	46	41	53	46	41	51	45	41	50	45	41					39				
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36					35				
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33					31				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	13173	13173	13173
5°	41304	11589	7181
10°	176292	9769	5310
15°	569657	7100	4239
20°	1174060	4358	2940
25°	1552364	2123	1796
30°	1665076	968	968
35°	1591293	663	361
40°	1485667	386	0
45°	1313107	0	0
50°	932401	461	0
55°	334254	516	0
60°	51606	1085	0
65°	2568	1284	0
70°	0	1587	0
75°	0	2097	1144
80°	0	3125	0
85°	0	6227	0



TEST NUMBER: P495111

CATALOG NUMBER: LDA2B108040R35D010 2LBD1MW-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4.7	0.6
10°-20°	63.9	8.1
20°-30°	214.0	27.1
30°-40°	269.6	34.1
40°-50°	190.7	24.1
50°-60°	44.0	5.6
60°-70°	1.4	0.2
70°-80°	0.9	0.1
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	282.6	35.8
0°-40°	552.2	69.9
0°-60°	786.9	99.6
0°-90°	790.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	790.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	27	27	27	27	27	
5°	83	54	23	17	14	15
15°	1115	197	14	10	8	368
25°	2852	311	4	4	3	1285
35°	2642	182	1	1	1	1654
45°	1882	45	0	0	0	1411
55°	389	2	1	1	0	440
65°	2	1	1	1	0	9
75°	0	1	1	1	1	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P495111

CATALOG NUMBER: LDA2B108040R35D010 2LBD1MW-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.7
1°	33.4	32.2	30.6	27.8	25.0	23.9	23.9	22.2	22.2
2°	40.0	38.4	35.0	29.5	25.0	22.2	21.1	20.0	19.5
3°	51.7	47.3	40.0	31.7	24.5	21.1	20.6	17.8	17.8
4°	64.5	60.0	46.1	33.4	23.9	20.0	17.8	16.7	16.1
5°	83.4	73.4	54.5	35.0	23.4	18.9	16.7	15.0	14.5
6°	107.9	94.0	62.3	36.7	22.8	17.8	15.6	13.9	13.3
7°	135.7	116.8	71.7	38.4	21.7	16.7	14.5	13.3	12.8
8°	194.6	150.1	82.8	39.5	21.1	15.6	13.9	12.2	11.7
9°	260.2	194.0	95.1	41.1	20.0	15.0	12.8	11.7	11.1
10°	351.9	254.1	109.0	42.3	19.5	13.9	11.7	11.1	10.6
11°	443.1	328.6	126.2	42.8	18.3	12.2	11.7	11.1	10.6
12°	593.2	399.8	141.2	42.8	17.2	11.7	10.6	10.0	9.5
13°	771.2	522.1	162.9	43.4	15.6	11.1	10.0	9.5	9.5
14°	928.0	631.6	177.4	43.4	15.0	10.0	9.5	9.5	8.9
15°	1115.3	738.4	196.8	42.8	13.9	9.5	9.5	8.9	8.3
16°	1311.6	898.5	223.0	41.7	12.8	8.3	8.9	7.8	7.2
17°	1571.8	1030.8	243.0	40.6	11.7	7.8	7.8	7.8	7.2
18°	1809.8	1191.5	259.1	39.5	10.6	7.8	7.2	7.2	6.7
19°	2065.0	1320.5	275.2	37.8	9.5	6.7	6.7	6.7	6.1
20°	2236.2	1478.9	293.0	36.1	8.3	6.1	6.7	6.1	5.6
21°	2453.0	1620.7	299.7	34.5	7.2	5.6	5.6	5.6	5.0
22.5°	2656.0	1809.2	310.2	31.1	6.1	4.4	5.0	4.4	4.4
23°	2687.1	1849.2	310.2	30.0	5.6	4.4	5.0	4.4	4.4
24°	2790.5	1958.8	314.1	27.8	4.4	3.9	4.4	3.9	3.9
25°	2851.7	2045.5	311.4	25.6	3.9	3.9	3.9	3.9	3.3
26°	2876.7	2069.4	304.7	23.9	3.3	3.3	3.9	3.3	2.8
27°	2902.8	2123.9	296.3	21.7	2.8	3.3	3.3	3.3	2.8
28°	2921.2	2130.6	288.0	20.0	2.2	2.8	3.3	2.8	2.8
29°	2927.3	2139.5	278.0	17.8	1.7	2.2	2.8	2.2	2.2
30°	2922.8	2137.8	263.5	16.1	1.7	2.2	2.2	2.2	1.7
32.5°	2837.8	2090.0	223.5	11.7	1.1	1.7	1.7	1.7	1.1
35°	2642.1	1979.9	182.4	7.8	1.1	1.1	1.1	1.1	0.6
37.5°	2487.5	1815.3	139.6	4.4	0.6	1.1	1.1	0.6	0.0
40°	2306.8	1576.8	100.6	2.8	0.6	0.6	0.6	0.0	0.0
42.5°	2123.3	1333.8	68.4	1.1	0.0	0.6	0.6	0.0	0.0
45°	1882.0	1021.4	45.0	0.6	0.0	0.6	0.0	0.0	0.0
47.5°	1582.9	741.7	30.6	0.0	0.0	0.6	0.0	0.0	0.0
50°	1214.8	415.3	17.2	0.0	0.6	0.6	0.6	0.0	0.0
52.5°	800.6	207.4	6.7	0.0	0.6	0.6	0.6	0.0	0.0
55°	388.6	111.2	2.2	0.6	0.6	1.1	0.6	0.0	0.0
57.5°	183.5	43.4	0.6	0.6	1.1	1.1	0.6	0.0	0.0
60°	52.3	8.9	0.6	0.6	1.1	1.1	0.6	0.6	0.0
62.5°	7.2	1.1	0.6	1.1	1.1	1.1	1.1	0.6	0.0
65°	2.2	0.6	0.6	1.1	1.1	1.1	1.1	0.6	0.0



TEST NUMBER: P495111

CATALOG NUMBER: LDA2B108040R35D010 2LBD1MW-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
67.5°	0.6	0.6	0.6	1.1	1.1	1.1	1.1	0.6	0.0
70°	0.0	0.6	0.6	1.1	1.1	1.1	1.1	0.6	0.0
72.5°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.0
75°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.6
77.5°	0.0	0.6	1.1	1.1	1.7	1.1	1.1	0.6	0.0
80°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.0
82.5°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.0
85°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.0
87.5°	0.0	0.6	1.1	1.1	1.1	1.1	0.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)