

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495113

Luminaire Tested: **LDA2B108040R35D010 2LBD1WH-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495113  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108040R35D010 2LBD1WH-30DEG TILT  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 790.0 lumens  
Efficiency: N/A  
Efficacy: 79.0 lumens/watt  
Spacing Criteria (0/90/45): 3.16 / 0.51 / 1.46  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495113

CATALOG NUMBER: LDA2B108040R35D010 2LBD1WH-30DEG TILT

### Luminous Intensity Polar Plot





TEST NUMBER: P495113

CATALOG NUMBER: LDA2B108040R35D010 2LBD1WH-30DEG TILT

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63
5	84	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56
6	77	66	58	53	76	65	58	52	63	57	52	62	56	52	60	55	51	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44
8	67	54	47	42	65	54	46	41	53	46	41	51	45	41	50	45	41	39
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	13173	13173	13173
5°	41304	11589	7181
10°	176292	9769	5310
15°	569657	7100	4239
20°	1174060	4358	2940
25°	1552364	2123	1796
30°	1665076	968	968
35°	1591293	663	361
40°	1485667	386	0
45°	1313107	0	0
50°	932401	461	0
55°	334254	516	0
60°	51606	1085	0
65°	2568	1284	0
70°	0	1587	0
75°	0	2097	1144
80°	0	3125	0
85°	0	6227	0



TEST NUMBER: P495113

CATALOG NUMBER: LDA2B108040R35D010 2LBD1WH-30DEG TILT

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	4.7	0.6
10°-20°	63.9	8.1
20°-30°	214.0	27.1
30°-40°	269.6	34.1
40°-50°	190.7	24.1
50°-60°	44.0	5.6
60°-70°	1.4	0.2
70°-80°	0.9	0.1
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	282.6	35.8
0°-40°	552.2	69.9
0°-60°	786.9	99.6
0°-90°	790.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	790.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	27	27	27	27	27	
5°	83	54	23	17	14	15
15°	1115	197	14	10	8	368
25°	2852	311	4	4	3	1285
35°	2642	182	1	1	1	1654
45°	1882	45	0	0	0	1411
55°	389	2	1	1	0	440
65°	2	1	1	1	0	9
75°	0	1	1	1	1	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P495113

CATALOG NUMBER: LDA2B108040R35D010 2LBD1WH-30DEG TILT

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.7
1°	33.4	32.2	30.6	27.8	25.0	23.9	23.9	22.2	22.2
2°	40.0	38.4	35.0	29.5	25.0	22.2	21.1	20.0	19.5
3°	51.7	47.3	40.0	31.7	24.5	21.1	20.6	17.8	17.8
4°	64.5	60.0	46.1	33.4	23.9	20.0	17.8	16.7	16.1
5°	83.4	73.4	54.5	35.0	23.4	18.9	16.7	15.0	14.5
6°	107.9	94.0	62.3	36.7	22.8	17.8	15.6	13.9	13.3
7°	135.7	116.8	71.7	38.4	21.7	16.7	14.5	13.3	12.8
8°	194.6	150.1	82.8	39.5	21.1	15.6	13.9	12.2	11.7
9°	260.2	194.0	95.1	41.1	20.0	15.0	12.8	11.7	11.1
10°	351.9	254.1	109.0	42.3	19.5	13.9	11.7	11.1	10.6
11°	443.1	328.6	126.2	42.8	18.3	12.2	11.7	11.1	10.6
12°	593.2	399.8	141.2	42.8	17.2	11.7	10.6	10.0	9.5
13°	771.2	522.1	162.9	43.4	15.6	11.1	10.0	9.5	9.5
14°	928.0	631.6	177.4	43.4	15.0	10.0	9.5	9.5	8.9
15°	1115.3	738.4	196.8	42.8	13.9	9.5	9.5	8.9	8.3
16°	1311.6	898.5	223.0	41.7	12.8	8.3	8.9	7.8	7.2
17°	1571.8	1030.8	243.0	40.6	11.7	7.8	7.8	7.8	7.2
18°	1809.8	1191.5	259.1	39.5	10.6	7.8	7.2	7.2	6.7
19°	2065.0	1320.5	275.2	37.8	9.5	6.7	6.7	6.7	6.1
20°	2236.2	1478.9	293.0	36.1	8.3	6.1	6.7	6.1	5.6
21°	2453.0	1620.7	299.7	34.5	7.2	5.6	5.6	5.6	5.0
22.5°	2656.0	1809.2	310.2	31.1	6.1	4.4	5.0	4.4	4.4
23°	2687.1	1849.2	310.2	30.0	5.6	4.4	5.0	4.4	4.4
24°	2790.5	1958.8	314.1	27.8	4.4	3.9	4.4	3.9	3.9
25°	2851.7	2045.5	311.4	25.6	3.9	3.9	3.9	3.9	3.3
26°	2876.7	2069.4	304.7	23.9	3.3	3.3	3.9	3.3	2.8
27°	2902.8	2123.9	296.3	21.7	2.8	3.3	3.3	3.3	2.8
28°	2921.2	2130.6	288.0	20.0	2.2	2.8	3.3	2.8	2.8
29°	2927.3	2139.5	278.0	17.8	1.7	2.2	2.8	2.2	2.2
30°	2922.8	2137.8	263.5	16.1	1.7	2.2	2.2	2.2	1.7
32.5°	2837.8	2090.0	223.5	11.7	1.1	1.7	1.7	1.7	1.1
35°	2642.1	1979.9	182.4	7.8	1.1	1.1	1.1	1.1	0.6
37.5°	2487.5	1815.3	139.6	4.4	0.6	1.1	1.1	0.6	0.0
40°	2306.8	1576.8	100.6	2.8	0.6	0.6	0.6	0.0	0.0
42.5°	2123.3	1333.8	68.4	1.1	0.0	0.6	0.6	0.0	0.0
45°	1882.0	1021.4	45.0	0.6	0.0	0.6	0.0	0.0	0.0
47.5°	1582.9	741.7	30.6	0.0	0.0	0.6	0.0	0.0	0.0
50°	1214.8	415.3	17.2	0.0	0.6	0.6	0.6	0.0	0.0
52.5°	800.6	207.4	6.7	0.0	0.6	0.6	0.6	0.0	0.0
55°	388.6	111.2	2.2	0.6	0.6	1.1	0.6	0.0	0.0
57.5°	183.5	43.4	0.6	0.6	1.1	1.1	0.6	0.0	0.0
60°	52.3	8.9	0.6	0.6	1.1	1.1	0.6	0.6	0.0
62.5°	7.2	1.1	0.6	1.1	1.1	1.1	1.1	0.6	0.0
65°	2.2	0.6	0.6	1.1	1.1	1.1	1.1	0.6	0.0



TEST NUMBER: P495113

CATALOG NUMBER: LDA2B108040R35D010 2LBD1WH-30DEG TILT

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
67.5°	0.6	0.6	0.6	1.1	1.1	1.1	1.1	0.6	0.0
70°	0.0	0.6	0.6	1.1	1.1	1.1	1.1	0.6	0.0
72.5°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.0
75°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.6
77.5°	0.0	0.6	1.1	1.1	1.7	1.1	1.1	0.6	0.0
80°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.0
82.5°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.0
85°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.0
87.5°	0.0	0.6	1.1	1.1	1.1	1.1	0.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)