

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223964

Luminaire Tested: **LD2B05D010 EU2B05SP159024 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223964
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B05SP159024 2LBDL*WH
Description: 500 Lumen, 2inch Portfolio LED Downlight
SPOT OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 293.0 lumens
Efficiency: N/A
Efficacy: 40.1 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223964

CATALOG NUMBER: LD2B05D010 EU2B05SP159024 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P223964

CATALOG NUMBER: LD2B05D010 EU2B05SP159024 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96						96													
3	110	106	103	101	108	105	102	100	102	100	98	100	99	97	98	97	96	94						94													
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93						93													
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	96	94	92	91						91													
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90						90													
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88						88													
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87						87													
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86						86													
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85						85													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1407925
5°	1017790
10°	296289
15°	103982
20°	44518
25°	20045
30°	7738
35°	3830
40°	2579
45°	1698
50°	904
55°	675
60°	387
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223964

CATALOG NUMBER: LD2B05D010 EU2B05SP159024 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.2	63.2
10°-20°	75.4	25.7
20°-30°	23.1	7.9
30°-40°	5.7	1.9
40°-50°	2.4	0.8
50°-60°	1.0	0.3
60°-70°	0.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	283.7	96.8
0°-40°	289.4	98.8
0°-60°	292.8	99.9
0°-90°	293.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	293.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3635	
5°	2618	185
15°	259	75
25°	47	23
35°	8	6
45°	3	2
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223964

CATALOG NUMBER: LD2B05D010 EU2B05SP159024 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3634.8
1°	3579.3
2°	3443.8
3°	3227.8
4°	2945.6
5°	2617.6
6°	2247.8
7°	1846.4
8°	1439.5
9°	1059.0
10°	753.3
11°	539.9
12°	406.0
13°	330.6
14°	289.3
15°	259.3
17.5°	159.9
20°	108.0
22.5°	72.3
25°	46.9
27.5°	28.5
30°	17.3
32.5°	11.2
35°	8.1
37.5°	6.6
40°	5.1
42.5°	4.1
45°	3.1
47.5°	2.0
50°	1.5
52.5°	1.5
55°	1.0
57.5°	1.0
60°	0.5
62.5°	0.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223964

CATALOG NUMBER: LD2B05D010 EU2B05SP159024 2LBDL*WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)