

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495182

Luminaire Tested: **LDA2B108040R60D010 2LBDL1WHH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495182  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108040R60D010 2LBDL1WHH  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1012.2 lumens  
Efficiency: N/A  
Efficacy: 101.2 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495182

CATALOG NUMBER: LDA2B108040R60D010 2LBDL1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P495182

CATALOG NUMBER: LDA2B108040R60D010 2LBDL1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	599089
5°	583499
10°	567402
15°	539266
20°	492736
25°	423135
30°	314865
35°	184841
40°	88104
45°	41096
50°	20493
55°	7139
60°	1677
65°	1284
70°	865
75°	1144
80°	0
85°	0



TEST NUMBER: P495182

CATALOG NUMBER: LDA2B108040R60D010 2LBDL1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.9	11.0
10°-20°	293.8	29.0
20°-30°	348.8	34.5
30°-40°	196.9	19.5
40°-50°	51.2	5.1
50°-60°	9.3	0.9
60°-70°	1.0	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	753.5	74.4
0°-40°	950.4	93.9
0°-60°	1010.9	99.9
0°-90°	1012.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1012.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1214	
5°	1178	111
15°	1056	294
25°	777	349
35°	307	197
45°	59	51
55°	8	9
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P495182

CATALOG NUMBER: LDA2B108040R60D010 2LBDL1WHH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1214.3
1°	1214.8
2°	1206.5
3°	1199.3
4°	1185.4
5°	1178.2
6°	1165.4
7°	1155.9
8°	1147.0
9°	1140.9
10°	1132.6
11°	1116.4
12°	1101.4
13°	1093.1
14°	1073.6
15°	1055.8
16°	1035.3
17°	1010.8
18°	987.4
19°	959.6
20°	938.5
21°	909.6
22.5°	861.8
23°	853.5
24°	812.9
25°	777.3
26°	737.8
27°	692.2
28°	647.2
29°	603.3
30°	552.7
32.5°	425.3
35°	306.9
37.5°	209.6
40°	136.8
42.5°	89.5
45°	58.9
47.5°	40.0
50°	26.7
52.5°	16.7
55°	8.3
57.5°	3.3
60°	1.7
62.5°	1.1
65°	1.1



TEST NUMBER: P495182

CATALOG NUMBER: LDA2B108040R60D010 2LBDL1WHH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)