

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495197

Luminaire Tested: **LDA2B108040R65D010 2LBDL1B**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P495197
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108040R65D010 2LBDL1B
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1040.8 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P495197
CATALOG NUMBER: LDA2B108040R65D010 2LBDL1B

Luminous Intensity Polar Plot





TEST NUMBER: P495197

CATALOG NUMBER: LDA2B108040R65D010 2LBDL1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72		79	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58		66	61	57		65	60	57	56
9	74	64	58	54	73	64	58	54	63	57	54		62	57	54		61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50		59	54	50		58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	544474
5°	521792
10°	496915
15°	472254
20°	439341
25°	405552
30°	351895
35°	252477
40°	137116
45°	58608
50°	25175
55°	9118
60°	1677
65°	1284
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P495197

CATALOG NUMBER: LDA2B108040R65D010 2LBDL1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.6	9.5
10°-20°	259.0	24.9
20°-30°	338.6	32.5
30°-40°	257.6	24.8
40°-50°	74.5	7.2
50°-60°	11.2	1.1
60°-70°	1.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	696.3	66.9
0°-40°	953.9	91.6
0°-60°	1039.6	99.9
0°-90°	1040.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1040.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1104	
5°	1054	99
15°	925	259
25°	745	339
35°	419	258
45°	84	74
55°	11	11
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495197

CATALOG NUMBER: LDA2B108040R65D010 2LBDL1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1103.6
1°	1099.8
2°	1093.6
3°	1081.4
4°	1068.1
5°	1053.6
6°	1039.7
7°	1027.5
8°	1015.8
9°	1005.2
10°	991.9
11°	980.2
12°	968.0
13°	955.8
14°	942.4
15°	924.6
16°	911.3
17°	895.2
18°	870.7
19°	857.9
20°	836.8
21°	817.9
22.5°	789.0
23°	777.8
24°	760.6
25°	745.0
26°	724.5
27°	701.7
28°	676.6
29°	650.0
30°	617.7
32.5°	529.3
35°	419.2
37.5°	309.1
40°	212.9
42.5°	135.1
45°	84.0
47.5°	52.3
50°	32.8
52.5°	19.5
55°	10.6
57.5°	3.9
60°	1.7
62.5°	1.1
65°	1.1



TEST NUMBER: P495197

CATALOG NUMBER: LDA2B108040R65D010 2LBDL1B

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)