

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264590

Luminaire Tested: **LD2B05D010 EU2B0510SP158027 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B0510SP158027 2LBDL*MW
Description: 500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 708.0 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264590

CATALOG NUMBER: LD2B05D010 EU2B0510SP158027 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P264590

CATALOG NUMBER: LD2B05D010 EU2B0510SP158027 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			100									
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97																			97									
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94																			94									
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92																			92									
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89																			89									
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87																			87									
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85																			85									
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83																			83									
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81																			81									
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79																			79									
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78																			78									

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2499371
5°	2034274
10°	1098833
15°	438135
20°	175673
25°	84104
30°	43638
35°	23067
40°	12816
45°	7884
50°	5449
55°	3699
60°	2763
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264590

CATALOG NUMBER: LD2B05D010 EU2B0510SP158027 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	330.3	46.7
10°-20°	260.6	36.8
20°-30°	76.9	10.9
30°-40°	25.6	3.6
40°-50°	9.6	1.4
50°-60°	4.3	0.6
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	667.8	94.3
0°-40°	693.4	97.9
0°-60°	707.3	99.9
0°-90°	708.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	708.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5066	
5°	4108	330
15°	858	261
25°	154	77
35°	38	26
45°	11	10
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264590

CATALOG NUMBER: LD2B05D010 EU2B0510SP158027 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5066.0
2.5°	4861.9
5°	4107.6
7.5°	3164.7
10°	2193.4
12.5°	1403.7
15°	857.8
17.5°	523.2
20°	334.6
22.5°	224.0
25°	154.5
27.5°	109.2
30°	76.6
32.5°	53.9
35°	38.3
37.5°	26.9
40°	19.9
42.5°	15.6
45°	11.3
47.5°	9.9
50°	7.1
52.5°	5.7
55°	4.3
57.5°	4.3
60°	2.8
62.5°	1.4
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)