

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P314973

Luminaire Tested: **LDA2B10NFL8040D010 PIN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P314973
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B10NFL8040D010 PIN1MW
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in Adj PinHole, Black oculus, matte white finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1033.1 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P314973

CATALOG NUMBER: LDA2B10NFL8040D010 PIN1MW

Luminous Intensity Polar Plot





TEST NUMBER: P314973

CATALOG NUMBER: LDA2B10NFL8040D010 PIN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97									97																		
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94									94																		
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91									91																		
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89									89																		
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86									86																		
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84									84																		
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82									82																		
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80									80																		
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78									78																		
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76									76																		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2644173
5°	2438544
10°	1643291
15°	810228
20°	346096
25°	136037
30°	53550
35°	23489
40°	11271
45°	5442
50°	2993
55°	1634
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P314973

CATALOG NUMBER: LDA2B10NFL8040D010 PIN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	417.1	40.4
10°-20°	449.2	43.5
20°-30°	129.7	12.6
30°-40°	27.4	2.6
40°-50°	6.7	0.7
50°-60°	1.9	0.2
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	996.0	96.4
0°-40°	1023.4	99.1
0°-60°	1032.0	99.9
0°-90°	1033.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1033.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5360	
5°	4924	417
15°	1586	449
25°	250	130
35°	39	27
45°	8	7
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P314973

CATALOG NUMBER: LDA2B10NFL8040D010 PIN1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5359.5
1°	5325.9
2°	5268.9
3°	5191.9
4°	5082.8
5°	4923.9
6°	4709.6
7°	4429.9
8°	4086.0
9°	3685.0
10°	3280.2
11°	2871.0
12°	2484.6
13°	2141.7
14°	1840.1
15°	1586.3
17.5°	1048.4
20°	659.2
22.5°	405.3
25°	249.9
27.5°	152.5
30°	94.0
32.5°	59.4
35°	39.0
37.5°	25.8
40°	17.5
42.5°	12.2
45°	7.8
47.5°	4.9
50°	3.9
52.5°	2.9
55°	1.9
57.5°	1.5
60°	1.0
62.5°	1.0
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P314973
CATALOG NUMBER: LDA2B10NFL8040D010 PIN1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)