

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224185

Luminaire Tested: **LD2B05D010 EU2B05SP158027 2LBD\*H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224185  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA ( 150)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B05D010 EU2B05SP158027 2LBD\*H  
Description: 500 Lumen, 2inch Portfolio LED Downlight  
SPOT OPTIC  
SPUN ROUND TRIM WITH HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 419.0 lumens  
Efficiency: N/A  
Efficacy: 57.4 lumens/watt  
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224185

CATALOG NUMBER: LD2B05D010 EU2B05SP158027 2LBD\*H

### Luminous Intensity Polar Plot





TEST NUMBER: P224185

CATALOG NUMBER: LD2B05D010 EU2B05SP158027 2LBD\*H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 106 | 104 | 103 | 103 | 101 | 100 | 100 | 98  | 98  | 98  | 98  |
| 2   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 104 | 105 | 103 | 102 | 102 | 101 | 100 | 100 | 99  | 98  | 96  | 96  | 96  | 96  |
| 3   | 110 | 106 | 103 | 101 | 108 | 105 | 102 | 100 | 102 | 100 | 98  | 100 | 98  | 97  | 98  | 97  | 96  | 94  | 94  | 94  | 94  |
| 4   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 97  | 100 | 98  | 96  | 98  | 96  | 95  | 97  | 95  | 94  | 93  | 93  | 93  | 93  |
| 5   | 105 | 101 | 97  | 95  | 104 | 100 | 97  | 94  | 98  | 96  | 94  | 97  | 95  | 93  | 95  | 94  | 92  | 91  | 91  | 91  | 91  |
| 6   | 103 | 98  | 95  | 93  | 102 | 98  | 95  | 92  | 96  | 94  | 92  | 95  | 93  | 91  | 94  | 92  | 91  | 90  | 90  | 90  | 90  |
| 7   | 101 | 96  | 93  | 91  | 100 | 96  | 93  | 90  | 95  | 92  | 90  | 94  | 91  | 90  | 93  | 91  | 89  | 88  | 88  | 88  | 88  |
| 8   | 100 | 94  | 91  | 89  | 99  | 94  | 91  | 89  | 93  | 90  | 89  | 92  | 90  | 88  | 92  | 90  | 88  | 87  | 87  | 87  | 87  |
| 9   | 98  | 93  | 90  | 88  | 97  | 92  | 89  | 87  | 92  | 89  | 87  | 91  | 89  | 87  | 90  | 88  | 87  | 86  | 86  | 86  | 86  |
| 10  | 96  | 91  | 88  | 86  | 96  | 91  | 88  | 86  | 90  | 88  | 86  | 90  | 87  | 86  | 89  | 87  | 86  | 85  | 85  | 85  | 85  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2013386 |
| 5°  | 1455491 |
| 10° | 423725  |
| 15° | 148695  |
| 20° | 63644   |
| 25° | 28635   |
| 30° | 11092   |
| 35° | 5532    |
| 40° | 3691    |
| 45° | 2410    |
| 50° | 1326    |
| 55° | 1013    |
| 60° | 542     |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P224185

CATALOG NUMBER: LD2B05D010 EU2B05SP158027 2LBD\*H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 264.9  | 63.2      |
| 10°-20°   | 107.8  | 25.7      |
| 20°-30°   | 33.1   | 7.9       |
| 30°-40°   | 8.2    | 1.9       |
| 40°-50°   | 3.4    | 0.8       |
| 50°-60°   | 1.5    | 0.4       |
| 60°-70°   | 0.3    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 405.7  | 96.8      |
| 0°-40°    | 413.9  | 98.8      |
| 0°-60°    | 418.8  | 99.9      |
| 0°-90°    | 419.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 419.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5198 |      |
| 5°  | 3743 | 265  |
| 15° | 371  | 108  |
| 25° | 67   | 33   |
| 35° | 12   | 8    |
| 45° | 4    | 3    |
| 55° | 2    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P224185

CATALOG NUMBER: LD2B05D010 EU2B05SP158027 2LBD\*H

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 5197.9 |
| 1°    | 5118.5 |
| 2°    | 4924.7 |
| 3°    | 4615.9 |
| 4°    | 4212.4 |
| 5°    | 3743.3 |
| 6°    | 3214.4 |
| 7°    | 2640.5 |
| 8°    | 2058.5 |
| 9°    | 1514.4 |
| 10°   | 1077.3 |
| 11°   | 772.1  |
| 12°   | 580.5  |
| 13°   | 472.7  |
| 14°   | 413.7  |
| 15°   | 370.8  |
| 17.5° | 228.7  |
| 20°   | 154.4  |
| 22.5° | 103.4  |
| 25°   | 67.0   |
| 27.5° | 40.8   |
| 30°   | 24.8   |
| 32.5° | 16.0   |
| 35°   | 11.7   |
| 37.5° | 9.5    |
| 40°   | 7.3    |
| 42.5° | 5.8    |
| 45°   | 4.4    |
| 47.5° | 2.9    |
| 50°   | 2.2    |
| 52.5° | 2.2    |
| 55°   | 1.5    |
| 57.5° | 1.5    |
| 60°   | 0.7    |
| 62.5° | 0.7    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P224185

CATALOG NUMBER: LD2B05D010 EU2B05SP158027 2LBD\*H

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |  |     |
|-------|--|-----|
| 85°   |  | 0.0 |
| 87.5° |  | 0.0 |



(END OF REPORT)