

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279496

Luminaire Tested: **LDA2B108050D010 EU2B10FL408050 2LBAD1WHH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279496
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B108050D010 EU2B10FL408050 2LBAD1WHH
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, WHH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1216.1 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279496

CATALOG NUMBER: LDA2B108050D010 EU2B10FL408050 2LBAD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P279496

CATALOG NUMBER: LDA2B108050D010 EU2B10FL408050 2LBAD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89			
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85			
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72			
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1672200
5°	1636839
10°	1491847
15°	1165414
20°	689987
25°	256505
30°	80155
35°	35655
40°	16552
45°	7814
50°	4298
55°	2408
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P279496

CATALOG NUMBER: LDA2B108050D010 EU2B10FL408050 2LBAD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	305.5	25.1
10°-20°	607.5	50.0
20°-30°	248.8	20.5
30°-40°	41.2	3.4
40°-50°	9.7	0.8
50°-60°	2.6	0.2
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1161.9	95.5
0°-40°	1203.1	98.9
0°-60°	1215.4	99.9
0°-90°	1216.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1216.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3389	
5°	3305	306
15°	2282	608
25°	471	249
35°	59	41
45°	11	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279496

CATALOG NUMBER: LDA2B108050D010 EU2B10FL408050 2LBAD1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3389.4
1°	3377.6
2°	3362.0
3°	3348.1
4°	3329.6
5°	3305.1
6°	3268.8
7°	3221.3
8°	3153.8
9°	3071.7
10°	2977.9
11°	2869.0
12°	2746.2
13°	2606.1
14°	2450.3
15°	2281.7
17.5°	1809.4
20°	1314.2
22.5°	841.3
25°	471.2
27.5°	248.4
30°	140.7
32.5°	89.3
35°	59.2
37.5°	39.1
40°	25.7
42.5°	16.7
45°	11.2
47.5°	7.8
50°	5.6
52.5°	3.9
55°	2.8
57.5°	1.7
60°	1.1
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279496

CATALOG NUMBER: LDA2B108050D010 EU2B10FL408050 2LBAD1WHH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)