

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264390

Luminaire Tested: **LD2B05D010 EU2B0510SP159040 2LBSQC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264390
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B0510SP159040 2LBSQC*MB
Description: 500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 610.0 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264390

CATALOG NUMBER: LD2B05D010 EU2B0510SP159040 2LBSQC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P264390

CATALOG NUMBER: LD2B05D010 EU2B0510SP159040 2LBSQC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2878371
5°	2307155
10°	1006955
15°	312078
20°	108785
25°	48067
30°	21762
35°	11323
40°	6440
45°	3070
50°	1919
55°	1118
60°	592
65°	700
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264390

CATALOG NUMBER: LD2B05D010 EU2B0510SP159040 2LBSQC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	353.8	58.0
10°-20°	193.7	31.8
20°-30°	44.2	7.2
30°-40°	12.7	2.1
40°-50°	3.9	0.6
50°-60°	1.2	0.2
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	591.7	97.0
0°-40°	604.4	99.1
0°-60°	609.5	99.9
0°-90°	610.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	610.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5834	
5°	4659	354
15°	611	194
25°	88	44
35°	19	13
45°	4	4
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264390

CATALOG NUMBER: LD2B05D010 EU2B0510SP159040 2LBSQC*MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	5834.2
1°	5761.5
2°	5610.7
3°	5376.6
4°	5054.8
5°	4658.6
6°	4172.8
7°	3630.1
8°	3063.6
9°	2515.2
10°	2010.0
11°	1582.5
12°	1245.7
13°	980.3
14°	774.3
15°	611.0
16°	482.0
17°	383.7
18°	308.6
19°	251.0
20°	207.2
22.5°	134.0
25°	88.3
26°	74.5
27°	63.2
28°	53.2
29°	44.4
30°	38.2
32.5°	26.3
35°	18.8
37.5°	13.8
40°	10.0
42.5°	6.9
45°	4.4
47.5°	3.1
50°	2.5
52.5°	1.9
55°	1.3
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6



TEST NUMBER: P264390

CATALOG NUMBER: LD2B05D010 EU2B0510SP159040 2LBSQC*MB

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)