

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279500

Luminaire Tested: **LDA2B108050D010 EU2B10FL408050 2LBALD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B108050D010 EU2B10FL408050 2LBALD1MW
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1219.6 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279500

CATALOG NUMBER: LDA2B108050D010 EU2B10FL408050 2LBALD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P279500

CATALOG NUMBER: LDA2B108050D010 EU2B10FL408050 2LBALD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1677035
5°	1641544
10°	1496155
15°	1168785
20°	691982
25°	257267
30°	80383
35°	35715
40°	16616
45°	7814
50°	4298
55°	2408
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P279500

CATALOG NUMBER: LDA2B108050D010 EU2B10FL408050 2LBALD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	306.4	25.1
10°-20°	609.3	50.0
20°-30°	249.6	20.5
30°-40°	41.3	3.4
40°-50°	9.8	0.8
50°-60°	2.6	0.2
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1165.2	95.5
0°-40°	1206.6	98.9
0°-60°	1218.9	99.9
0°-90°	1219.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1219.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3399	
5°	3315	306
15°	2288	609
25°	473	250
35°	59	41
45°	11	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279500

CATALOG NUMBER: LDA2B108050D010 EU2B10FL408050 2LBALD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3399.2
1°	3387.4
2°	3371.7
3°	3357.7
4°	3339.3
5°	3314.6
6°	3278.2
7°	3230.6
8°	3162.9
9°	3080.6
10°	2986.5
11°	2877.3
12°	2754.2
13°	2613.6
14°	2457.4
15°	2288.3
17.5°	1814.6
20°	1318.0
22.5°	843.8
25°	472.6
27.5°	249.2
30°	141.1
32.5°	89.6
35°	59.3
37.5°	39.2
40°	25.8
42.5°	16.8
45°	11.2
47.5°	7.8
50°	5.6
52.5°	3.9
55°	2.8
57.5°	1.7
60°	1.1
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279500

CATALOG NUMBER: LDA2B108050D010 EU2B10FL408050 2LBALD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)