

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495270

Luminaire Tested: **LDA2B108050R20D010 2LBDLC1MB-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P495270
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108050R20D010 2LBDLC1MB-30DEG TILT
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 720.5 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P495270

CATALOG NUMBER: LDA2B108050R20D010 2LBDLC1MB-30DEG TILT

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P495270

CATALOG NUMBER: LDA2B108050R20D010 2LBDLC1MB-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91					91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82					82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74					74			
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66					66			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59					59			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53					53			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48					48			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43					43			
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38					38			
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	11446	11446	11446
5°	21890	10103	7379
10°	52302	8867	4960
15°	304723	7049	1992
20°	1519946	4358	578
25°	2771469	1524	0
30°	3250623	0	0
35°	2845127	0	0
40°	2101045	0	0
45°	757304	0	0
50°	157728	0	0
55°	36126	516	0
60°	11446	592	0
65°	2568	1284	0
70°	0	1587	865
75°	0	2097	0
80°	0	3125	0
85°	0	6227	0



TEST NUMBER: P495270

CATALOG NUMBER: LDA2B108050R20D010 2LBDLC1MB-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2.6	0.4
10°-20°	39.6	5.5
20°-30°	266.8	37.0
30°-40°	311.7	43.3
40°-50°	90.9	12.6
50°-60°	6.1	0.8
60°-70°	1.2	0.2
70°-80°	0.9	0.1
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	309.0	42.9
0°-40°	620.7	86.1
0°-60°	717.7	99.6
0°-90°	720.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	720.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	23	23	23	23	23	
5°	44	32	20	17	15	6
15°	597	67	14	7	4	311
25°	5091	104	3	0	0	2254
35°	4724	56	0	0	0	2902
45°	1085	12	0	0	0	1000
55°	42	2	1	1	0	53
65°	2	1	1	1	0	3
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P495270

CATALOG NUMBER: LDA2B108050R20D010 2LBDLC1MB-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	23.2	23.2	23.2	23.2	23.2	23.2	23.2	23.2	23.2
2.5°	29.8	29.8	26.5	23.8	21.5	20.4	19.9	18.8	18.2
5°	44.2	38.7	32.0	24.9	20.4	18.8	17.1	15.5	14.9
7.5°	64.6	56.3	38.7	25.4	19.3	16.6	14.9	13.3	12.2
10°	104.4	81.2	47.5	25.4	17.7	14.4	12.2	10.5	9.9
12.5°	192.8	124.3	56.9	24.9	16.0	12.2	9.4	8.3	6.6
15°	596.6	257.4	67.4	23.8	13.8	9.4	7.2	4.4	3.9
17.5°	1542.8	601.0	75.1	21.0	11.0	6.6	3.3	2.8	2.8
20°	2895.0	1089.8	86.2	18.2	8.3	4.4	2.2	1.7	1.1
21°	3302.6	1333.4	91.7	17.1	7.2	2.8	1.7	0.6	0.6
22°	3936.2	1599.1	96.1	16.0	6.1	1.7	1.1	0.6	0.0
23°	4387.5	1768.7	100.5	14.4	4.4	1.7	0.6	0.0	0.0
24°	4838.7	1984.7	103.3	13.3	3.9	1.1	0.6	0.0	0.0
25°	5091.2	2164.7	104.4	12.2	2.8	0.6	0.0	0.0	0.0
26°	5298.9	2285.1	104.9	11.0	1.7	0.0	0.0	0.0	0.0
27°	5476.7	2424.9	103.8	9.9	1.7	0.0	0.0	0.0	0.0
28°	5577.8	2448.1	102.2	8.8	0.6	0.0	0.0	0.0	0.0
29°	5621.4	2419.9	97.2	7.7	0.6	0.0	0.0	0.0	0.0
30°	5706.0	2393.4	92.2	7.2	0.0	0.0	0.0	0.0	0.0
31°	5628.1	2305.6	86.2	6.1	0.0	0.0	0.0	0.0	0.0
32°	5323.2	2231.6	79.0	5.0	0.0	0.0	0.0	0.0	0.0
33°	5232.0	2079.7	71.3	4.4	0.0	0.0	0.0	0.0	0.0
34°	5060.2	1853.7	64.6	3.9	0.0	0.0	0.0	0.0	0.0
35°	4723.9	1667.0	56.3	3.3	0.0	0.0	0.0	0.0	0.0
36°	4489.1	1453.8	49.2	2.8	0.0	0.0	0.0	0.0	0.0
37°	4243.3	1267.7	43.6	2.2	0.0	0.0	0.0	0.0	0.0
38°	3937.8	1072.1	37.0	1.7	0.0	0.0	0.0	0.0	0.0
39°	3582.1	886.0	31.5	1.7	0.0	0.0	0.0	0.0	0.0
40°	3262.3	714.2	27.1	1.1	0.0	0.0	0.0	0.0	0.0
42.5°	2013.4	407.6	16.0	1.1	0.0	0.0	0.0	0.0	0.0
45°	1085.4	247.5	11.6	0.6	0.0	0.0	0.0	0.0	0.0
47.5°	499.9	115.4	8.3	0.6	0.0	0.0	0.0	0.0	0.0
50°	205.5	51.4	6.1	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	74.0	28.7	3.9	0.0	0.0	0.6	0.0	0.0	0.0
55°	42.0	16.6	2.2	0.6	0.6	0.6	0.6	0.0	0.0
57.5°	19.9	9.4	0.6	0.6	0.6	0.6	0.6	0.0	0.0
60°	11.6	5.0	0.6	0.6	0.6	1.1	0.6	0.0	0.0
62.5°	5.5	1.7	0.6	1.1	1.1	1.1	1.1	0.6	0.0
65°	2.2	0.6	1.1	1.1	1.1	1.7	1.1	0.6	0.0
67.5°	0.6	0.6	1.1	1.1	1.1	1.7	1.1	0.6	0.6
70°	0.0	0.6	1.1	1.1	1.1	1.7	1.1	0.6	0.6
72.5°	0.0	0.6	1.1	1.1	1.1	1.7	1.1	0.6	0.6
75°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.0
77.5°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.0
80°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.0



TEST NUMBER: P495270

CATALOG NUMBER: LDA2B108050R20D010 2LBDLC1MB-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.0
85°	0.0	0.6	1.1	1.1	1.1	1.1	1.1	0.6	0.0
87.5°	0.0	0.6	1.1	1.1	1.1	1.1	0.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)