

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495311

Luminaire Tested: **LDA2B108050R30D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P495311
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-16)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108050R30D010 2LBDLC1MMS
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1054.3 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P495311

CATALOG NUMBER: LDA2B108050R30D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P495311

CATALOG NUMBER: LDA2B108050R30D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94		97	95	93		95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91		94	92	90		92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87		91	89	86		90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84		89	86	84		88	85	83	82
7	96	89	85	82	95	89	85	82	87	84	81		86	83	81		85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79		84	81	79		83	80	78	77
9	90	84	80	77	90	83	80	77	83	79	77		82	79	76		81	78	76	75
10	88	81	77	75	87	81	77	75	80	77	75		80	77	74		79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2043061
5°	1948002
10°	1579817
15°	965756
20°	421962
25°	157866
30°	65457
35°	30596
40°	14233
45°	6907
50°	3838
55°	1462
60°	592
65°	700
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P495311

CATALOG NUMBER: LDA2B108050R30D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	350.9	33.3
10°-20°	506.6	48.1
20°-30°	151.2	14.3
30°-40°	34.7	3.3
40°-50°	8.6	0.8
50°-60°	2.0	0.2
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1008.7	95.7
0°-40°	1043.4	99.0
0°-60°	1053.9	100.0
0°-90°	1054.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1054.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4141	
5°	3933	351
15°	1891	507
25°	290	151
35°	51	35
45°	10	9
55°	2	2
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495311

CATALOG NUMBER: LDA2B108050R30D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	4141.1
1°	4131.7
2°	4089.7
3°	4061.6
4°	4009.1
5°	3933.4
6°	3830.1
7°	3706.9
8°	3550.1
9°	3359.0
10°	3153.5
11°	2933.6
12°	2684.0
13°	2415.5
14°	2160.3
15°	1890.8
16°	1630.0
17°	1373.2
18°	1166.0
19°	965.0
20°	803.7
21°	651.2
22.5°	482.8
23°	435.3
24°	356.3
25°	290.0
26°	238.1
27°	198.3
28°	163.5
29°	137.0
30°	114.9
32.5°	75.1
35°	50.8
37.5°	33.7
40°	22.1
42.5°	14.4
45°	9.9
47.5°	7.2
50°	5.0
52.5°	3.3
55°	1.7
57.5°	1.1
60°	0.6
62.5°	0.6
65°	0.6



TEST NUMBER: P495311

CATALOG NUMBER: LDA2B108050R30D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)