

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495318

Luminaire Tested: **LDA2B108050R35D010 2LBD1GPH**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495318  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/12/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108050R35D010 2LBD1GPH  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1127.0 lumens  
Efficiency: N/A  
Efficacy: 112.7 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495318

CATALOG NUMBER: LDA2B108050R35D010 2LBD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P495318

CATALOG NUMBER: LDA2B108050R35D010 2LBD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98	100	98	96	97	95	94	93
3	107	102	99	96	105	101	98	95	99	96	93	96	94	92	94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75
9	89	82	77	75	88	81	77	74	80	77	74	80	76	74	79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1771070
5°	1703746
10°	1542996
15°	1074089
20°	526390
25°	196352
30°	86193
35°	41919
40°	19192
45°	10396
50°	5066
55°	1462
60°	592
65°	700
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P495318

CATALOG NUMBER: LDA2B108050R35D010 2LBD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	317.8	28.2
10°-20°	557.2	49.4
20°-30°	189.9	16.8
30°-40°	47.2	4.2
40°-50°	12.2	1.1
50°-60°	2.3	0.2
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1064.9	94.5
0°-40°	1112.1	98.7
0°-60°	1126.5	100.0
0°-90°	1127.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1127.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3590	
5°	3440	318
15°	2103	557
25°	361	190
35°	70	47
45°	15	12
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495318

CATALOG NUMBER: LDA2B108050R35D010 2LBD1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3589.8
1°	3582.7
2°	3555.0
3°	3528.5
4°	3486.0
5°	3440.2
6°	3395.4
7°	3353.4
8°	3262.8
9°	3175.0
10°	3080.0
11°	2924.2
12°	2755.2
13°	2537.6
14°	2336.0
15°	2102.9
16°	1875.3
17°	1638.3
18°	1416.8
19°	1192.6
20°	1002.6
21°	821.4
22.5°	602.6
23°	541.3
24°	441.9
25°	360.7
26°	298.3
27°	249.1
28°	209.9
29°	177.3
30°	151.3
32.5°	102.7
35°	69.6
37.5°	47.0
40°	29.8
42.5°	20.4
45°	14.9
47.5°	10.5
50°	6.6
52.5°	3.9
55°	1.7
57.5°	1.1
60°	0.6
62.5°	0.6
65°	0.6



TEST NUMBER: P495318

CATALOG NUMBER: LDA2B108050R35D010 2LBD1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)