

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265172

Luminaire Tested: **LD2B05D010 EU2B0510SP159727 2LBSQLC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P265172  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B05D010 EU2B0510SP159727 2LBSQLC\*MMS  
Description: 500 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 452.0 lumens  
Efficiency: N/A  
Efficacy: 61.9 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P265172

CATALOG NUMBER: LD2B05D010 EU2B0510SP159727 2LBSQLC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P265172

CATALOG NUMBER: LD2B05D010 EU2B0510SP159727 2LBSQLC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92
4	106	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	79	78

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1595631
5°	1298685
10°	701512
15°	279695
20°	112145
25°	53729
30°	27858
35°	14696
40°	8179
45°	5024
50°	3454
55°	2322
60°	1776
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265172

CATALOG NUMBER: LD2B05D010 EU2B0510SP159727 2LBSQLC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	210.9	46.7
10°-20°	166.4	36.8
20°-30°	49.1	10.9
30°-40°	16.3	3.6
40°-50°	6.1	1.4
50°-60°	2.7	0.6
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	426.4	94.3
0°-40°	442.7	97.9
0°-60°	451.5	99.9
0°-90°	452.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	452.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3234	
5°	2622	211
15°	548	166
25°	99	49
35°	24	16
45°	7	6
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265172

CATALOG NUMBER: LD2B05D010 EU2B0510SP159727 2LBSQLC\*MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3234.2
2.5°	3103.9
5°	2622.3
7.5°	2020.4
10°	1400.3
12.5°	896.1
15°	547.6
17.5°	334.0
20°	213.6
22.5°	143.0
25°	98.7
27.5°	69.7
30°	48.9
32.5°	34.4
35°	24.4
37.5°	17.2
40°	12.7
42.5°	10.0
45°	7.2
47.5°	6.3
50°	4.5
52.5°	3.6
55°	2.7
57.5°	2.7
60°	1.8
62.5°	0.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)