

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495395

Luminaire Tested: **LDA2B108050R60D010 2LBDL1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495395  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108050R60D010 2LBDL1MMS  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1005.7 lumens  
Efficiency: N/A  
Efficacy: 100.6 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495395

CATALOG NUMBER: LDA2B108050R60D010 2LBDL1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P495395

CATALOG NUMBER: LDA2B108050R60D010 2LBDL1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	595192
5°	579686
10°	563694
15°	535742
20°	489533
25°	420358
30°	312814
35°	183636
40°	87525
45°	40886
50°	20340
55°	7139
60°	1677
65°	1284
70°	865
75°	1144
80°	0
85°	0



TEST NUMBER: P495395

CATALOG NUMBER: LDA2B108050R60D010 2LBDL1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.1	11.0
10°-20°	291.9	29.0
20°-30°	346.6	34.5
30°-40°	195.6	19.4
40°-50°	50.9	5.1
50°-60°	9.3	0.9
60°-70°	1.0	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	748.6	74.4
0°-40°	944.2	93.9
0°-60°	1004.3	99.9
0°-90°	1005.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1005.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1206	
5°	1170	110
15°	1049	292
25°	772	347
35°	305	196
45°	59	51
55°	8	9
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P495395

CATALOG NUMBER: LDA2B108050R60D010 2LBDL1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1206.4
1°	1206.9
2°	1198.6
3°	1191.5
4°	1177.7
5°	1170.5
6°	1157.8
7°	1148.4
8°	1139.5
9°	1133.5
10°	1125.2
11°	1109.2
12°	1094.2
13°	1086.0
14°	1066.6
15°	1048.9
16°	1028.5
17°	1004.2
18°	981.0
19°	953.4
20°	932.4
21°	903.7
22.5°	856.2
23°	847.9
24°	807.6
25°	772.2
26°	733.0
27°	687.7
28°	643.0
29°	599.3
30°	549.1
32.5°	422.6
35°	304.9
37.5°	208.2
40°	135.9
42.5°	88.9
45°	58.6
47.5°	39.8
50°	26.5
52.5°	16.6
55°	8.3
57.5°	3.3
60°	1.7
62.5°	1.1
65°	1.1



TEST NUMBER: P495395

CATALOG NUMBER: LDA2B108050R60D010 2LBDL1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)