

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222379

Luminaire Tested: **LD2B05D010 EU2B05NFL259727 2LBDSQLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222379
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B05NFL259727 2LBDSQLC*MMS
Description: 500 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 469.0 lumens
Efficiency: N/A
Efficacy: 64.2 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222379

CATALOG NUMBER: LD2B05D010 EU2B05NFL259727 2LBDSQLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P222379

CATALOG NUMBER: LD2B05D010 EU2B05NFL259727 2LBDSQLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97				97															
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95				95															
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92				92															
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90				90															
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88				88															
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86				86															
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84				84															
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82				82															
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80				80															
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79				79															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1077751
5°	995121
10°	673563
15°	229137
20°	84172
25°	44619
30°	22945
35°	10687
40°	3489
45°	1753
50°	844
55°	338
60°	387
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222379

CATALOG NUMBER: LD2B05D010 EU2B05NFL259727 2LBDSQLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.7	46.4
10°-20°	183.0	39.0
20°-30°	50.2	10.7
30°-40°	14.6	3.1
40°-50°	2.7	0.6
50°-60°	0.6	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	451.0	96.2
0°-40°	465.6	99.3
0°-60°	468.9	100.0
0°-90°	469.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	469.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2782	
5°	2559	218
15°	571	183
25°	104	50
35°	23	15
45°	3	3
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222379

CATALOG NUMBER: LD2B05D010 EU2B05NFL259727 2LBDSQLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2782.4
1°	2766.2
2°	2737.6
3°	2696.5
4°	2640.1
5°	2559.3
6°	2448.9
7°	2310.7
8°	2142.1
9°	1943.0
10°	1712.5
11°	1459.8
12°	1196.9
13°	946.1
14°	732.2
15°	571.4
17.5°	322.4
20°	204.2
22.5°	145.5
25°	104.4
27.5°	73.9
30°	51.3
32.5°	36.0
35°	22.6
37.5°	9.2
40°	6.9
42.5°	5.1
45°	3.2
47.5°	1.8
50°	1.4
52.5°	0.9
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222379

CATALOG NUMBER: LD2B05D010 EU2B05NFL259727 2LBDSQLC*MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)