

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495420

Luminaire Tested: **LDA2B108050R65D010 2LBDL1WH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495420  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108050R65D010 2LBDL1WH  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1034.0 lumens  
Efficiency: N/A  
Efficacy: 103.4 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495420  
CATALOG NUMBER: LDA2B108050R65D010 2LBDL1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P495420

CATALOG NUMBER: LDA2B108050R65D010 2LBDL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72		79	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58		66	61	57		65	60	57	56
9	74	64	58	54	73	64	58	54	63	57	54		62	57	54		61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50		59	54	50		58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	540971
5°	518374
10°	493658
15°	469189
20°	436453
25°	402939
30°	349616
35°	250851
40°	136278
45°	58190
50°	25022
55°	9032
60°	1677
65°	1284
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P495420

CATALOG NUMBER: LDA2B108050R65D010 2LBDL1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	98.0	9.5
10°-20°	257.3	24.9
20°-30°	336.4	32.5
30°-40°	255.9	24.8
40°-50°	74.0	7.2
50°-60°	11.1	1.1
60°-70°	1.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	691.7	66.9
0°-40°	947.7	91.7
0°-60°	1032.8	99.9
0°-90°	1034.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1034.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1096	
5°	1047	98
15°	919	257
25°	740	336
35°	416	256
45°	83	74
55°	10	11
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495420

CATALOG NUMBER: LDA2B108050R65D010 2LBDL1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1096.5
1°	1092.6
2°	1086.5
3°	1074.4
4°	1061.1
5°	1046.7
6°	1032.9
7°	1020.8
8°	1009.2
9°	998.7
10°	985.4
11°	973.8
12°	961.7
13°	949.5
14°	936.3
15°	918.6
16°	905.3
17°	889.3
18°	865.0
19°	852.3
20°	831.3
21°	812.5
22.5°	783.8
23°	772.8
24°	755.6
25°	740.2
26°	719.7
27°	697.1
28°	672.2
29°	645.7
30°	613.7
32.5°	525.9
35°	416.5
37.5°	307.1
40°	211.6
42.5°	134.2
45°	83.4
47.5°	51.9
50°	32.6
52.5°	19.3
55°	10.5
57.5°	3.9
60°	1.7
62.5°	1.1
65°	1.1



TEST NUMBER: P495420

CATALOG NUMBER: LDA2B108050R65D010 2LBDL1WH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)