

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B05D010 EU2B0510SP158030 2LBPIN**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14823)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B0510SP158030 2LBPIN
Description: 500 Lumen, 2inch Portfolio LED Downlight
SPOT OPTIC
ROUND PINHOLE BLACK OCULUS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 361.9 lumens
Efficiency: N/A
Efficacy: 49.6 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.24
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B0510SP158030 2LBPIN

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B0510SP158030 2LBPIN

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	95																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	105	101	97	95	104	100	97	95	98	96	94	97	95	93	96	94	92	91																			
6	103	98	95	93	102	98	95	93	97	94	92	95	93	91	94	92	91	90																			
7	102	96	93	91	101	96	93	91	95	92	90	94	92	90	93	91	89	89																			
8	100	95	91	89	99	94	91	89	93	91	89	93	90	88	92	90	88	87																			
9	98	93	90	88	97	93	90	88	92	89	87	91	89	87	91	89	87	86																			
10	97	92	88	86	96	91	88	86	91	88	86	90	88	86	90	87	86	85																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1660763
5°	1231232
10°	382840
15°	121991
20°	53152
25°	23558
30°	8725
35°	4210
40°	2883
45°	1754
50°	965
55°	1081
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B0510SP158030 2LBPIN

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.9	63.3
10°-20°	95.7	26.4
20°-30°	27.4	7.6
30°-40°	6.2	1.7
40°-50°	2.5	0.7
50°-60°	1.2	0.3
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	352.0	97.3
0°-40°	358.1	99.0
0°-60°	361.8	100.0
0°-90°	361.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	361.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4286	
5°	3165	229
15°	304	96
25°	55	27
35°	9	6
45°	3	3
55°	2	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B0510SP158030 2LBPIN

CANDELA DISTRIBUTION (FULL):

	0°
0°	4286.0
2.5°	4018.4
5°	3165.4
7.5°	2018.1
10°	973.0
12.5°	452.4
15°	304.1
17.5°	188.9
20°	128.9
22.5°	87.6
25°	55.1
27.5°	32.4
30°	19.5
32.5°	12.2
35°	8.9
37.5°	6.5
40°	5.7
42.5°	4.1
45°	3.2
47.5°	2.4
50°	1.6
52.5°	1.6
55°	1.6
57.5°	0.8
60°	0.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)