

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495546

Luminaire Tested: **LDA2B109024R35D010 2LBD1WH**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495546  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/12/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109024R35D010 2LBD1WH  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 773.4 lumens  
Efficiency: N/A  
Efficacy: 77.3 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495546

CATALOG NUMBER: LDA2B109024R35D010 2LBD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P495546

CATALOG NUMBER: LDA2B109024R35D010 2LBD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100	99	98	96
2	111	107	104	101	109	106	103	100	102	100	98		100	98	96		97	95	94	93
3	107	102	99	96	105	101	98	95	99	96	93		96	94	92		94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81	78	76	75
9	89	82	77	75	88	81	77	74	80	77	74		80	76	74		79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77	74	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1215397
5°	1169178
10°	1058856
15°	737086
20°	361217
25°	134730
30°	59190
35°	28789
40°	13203
45°	7117
50°	3454
55°	946
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P495546

CATALOG NUMBER: LDA2B109024R35D010 2LBD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	218.1	28.2
10°-20°	382.4	49.4
20°-30°	130.3	16.8
30°-40°	32.4	4.2
40°-50°	8.3	1.1
50°-60°	1.5	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	730.8	94.5
0°-40°	763.2	98.7
0°-60°	773.1	100.0
0°-90°	773.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	773.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2464	
5°	2361	218
15°	1443	382
25°	248	130
35°	48	32
45°	10	8
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495546

CATALOG NUMBER: LDA2B109024R35D010 2LBD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2463.5
1°	2458.6
2°	2439.6
3°	2421.4
4°	2392.3
5°	2360.8
6°	2330.1
7°	2301.3
8°	2239.1
9°	2178.8
10°	2113.6
11°	2006.7
12°	1890.8
13°	1741.4
14°	1603.0
15°	1443.1
16°	1286.9
17°	1124.3
18°	972.3
19°	818.4
20°	688.0
21°	563.7
22.5°	413.6
23°	371.5
24°	303.2
25°	247.5
26°	204.7
27°	171.0
28°	144.0
29°	121.7
30°	103.9
32.5°	70.5
35°	47.8
37.5°	32.2
40°	20.5
42.5°	14.0
45°	10.2
47.5°	7.2
50°	4.5
52.5°	2.7
55°	1.1
57.5°	0.8
60°	0.4
62.5°	0.4
65°	0.4



TEST NUMBER: P495546

CATALOG NUMBER: LDA2B109024R35D010 2LBD1WH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)