

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224811

Luminaire Tested: **LD2B05D010 EU2B05FL409030 2LBDL*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224811
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B05FL409030 2LBDL*B
Description: 500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 572.0 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224811

CATALOG NUMBER: LD2B05D010 EU2B05FL409030 2LBDL*B

Luminous Intensity Polar Plot





TEST NUMBER: P224811

CATALOG NUMBER: LD2B05D010 EU2B05FL409030 2LBDL*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	103	100	108	104	101	99	101	99	96	98	96	94	96	94	92	91			91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87			87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83			83
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79			79
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76			76
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72			72
8	87	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	69			69
9	84	77	72	69	83	76	72	68	75	71	68	74	71	68	74	70	68	67			67
10	82	74	69	66	81	73	69	66	73	68	65	72	68	65	71	68	65	64			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	517533
5°	508545
10°	453657
15°	358583
20°	239120
25°	138730
30°	69416
35°	32675
40°	12793
45°	5697
50°	2712
55°	1486
60°	542
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224811

CATALOG NUMBER: LD2B05D010 EU2B05FL409030 2LBDL*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.9	21.0
10°-20°	242.0	42.3
20°-30°	152.3	26.6
30°-40°	46.5	8.1
40°-50°	9.1	1.6
50°-60°	2.1	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	514.2	89.9
0°-40°	560.7	98.0
0°-60°	571.9	100.0
0°-90°	572.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	572.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1336	
5°	1308	120
15°	894	242
25°	325	152
35°	69	47
45°	10	9
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224811

CATALOG NUMBER: LD2B05D010 EU2B05FL409030 2LBDL*B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1336.1
2.5°	1333.2
5°	1307.9
7.5°	1248.5
10°	1153.4
12.5°	1034.6
15°	894.2
17.5°	738.2
20°	580.1
22.5°	444.9
25°	324.6
27.5°	228.8
30°	155.2
32.5°	104.7
35°	69.1
37.5°	42.3
40°	25.3
42.5°	16.3
45°	10.4
47.5°	6.7
50°	4.5
52.5°	3.0
55°	2.2
57.5°	1.5
60°	0.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)