

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495595

Luminaire Tested: **LDA2B109024R45D010 2LBDLC1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P495595
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109024R45D010 2LBDLC1MW
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 783.4 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P495595

CATALOG NUMBER: LDA2B109024R45D010 2LBDLC1MW

Luminous Intensity Polar Plot





TEST NUMBER: P495595

CATALOG NUMBER: LDA2B109024R45D010 2LBDLC1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80	86	82	80	84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66	73	69	66	72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63	70	66	63	69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	776551
5°	759411
10°	704568
15°	600865
20°	452361
25°	272727
30°	131483
35°	59626
40°	27436
45°	14164
50°	7445
55°	2752
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P495595

CATALOG NUMBER: LDA2B109024R45D010 2LBDLC1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.6	18.2
10°-20°	321.3	41.0
20°-30°	229.5	29.3
30°-40°	68.8	8.8
40°-50°	17.1	2.2
50°-60°	3.5	0.5
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	693.3	88.5
0°-40°	762.1	97.3
0°-60°	782.7	99.9
0°-90°	783.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	783.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1574	
5°	1533	143
15°	1176	321
25°	501	230
35°	99	69
45°	20	17
55°	3	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495595

CATALOG NUMBER: LDA2B109024R45D010 2LBDLC1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1574.0
1°	1576.8
2°	1573.2
3°	1559.8
4°	1550.0
5°	1533.4
6°	1516.8
7°	1498.9
8°	1469.7
9°	1442.1
10°	1406.4
11°	1370.7
12°	1325.7
13°	1277.4
14°	1232.4
15°	1176.4
16°	1121.7
17°	1059.6
18°	1000.8
19°	928.6
20°	861.6
21°	787.4
22.5°	676.6
23°	639.3
24°	566.7
25°	501.0
26°	435.3
27°	375.2
28°	319.3
29°	273.4
30°	230.8
32.5°	151.7
35°	99.0
37.5°	64.9
40°	42.6
42.5°	28.8
45°	20.3
47.5°	14.6
50°	9.7
52.5°	6.1
55°	3.2
57.5°	1.6
60°	0.8
62.5°	0.8
65°	0.4



TEST NUMBER: P495595

CATALOG NUMBER: LDA2B109024R45D010 2LBDLC1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)