

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495609

Luminaire Tested: **LDA2B109024R60D010 2LBDL1LI**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495609  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109024R60D010 2LBDL1LI  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 690.1 lumens  
Efficiency: N/A  
Efficacy: 69.0 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495609  
CATALOG NUMBER: LDA2B109024R60D010 2LBDL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P495609

CATALOG NUMBER: LDA2B109024R60D010 2LBDL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54		61	57	54		61	57	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	408454
5°	397782
10°	386801
15°	367649
20°	335963
25°	288459
30°	214657
35°	125998
40°	60024
45°	28048
50°	13969
55°	4903
60°	1085
65°	934
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P495609

CATALOG NUMBER: LDA2B109024R60D010 2LBDL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.6	11.0
10°-20°	200.3	29.0
20°-30°	237.8	34.5
30°-40°	134.2	19.4
40°-50°	34.9	5.1
50°-60°	6.4	0.9
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	513.7	74.4
0°-40°	647.9	93.9
0°-60°	689.2	99.9
0°-90°	690.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	690.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	828	
5°	803	76
15°	720	200
25°	530	238
35°	209	134
45°	40	35
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495609

CATALOG NUMBER: LDA2B109024R60D010 2LBDL1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	827.9
1°	828.2
2°	822.6
3°	817.6
4°	808.2
5°	803.2
6°	794.5
7°	788.1
8°	782.0
9°	777.8
10°	772.1
11°	761.2
12°	750.9
13°	745.2
14°	732.0
15°	719.8
16°	705.8
17°	689.1
18°	673.2
19°	654.3
20°	639.9
21°	620.1
22.5°	587.5
23°	581.9
24°	554.2
25°	529.9
26°	503.0
27°	471.9
28°	441.2
29°	411.3
30°	376.8
32.5°	290.0
35°	209.2
37.5°	142.9
40°	93.2
42.5°	61.0
45°	40.2
47.5°	27.3
50°	18.2
52.5°	11.4
55°	5.7
57.5°	2.3
60°	1.1
62.5°	0.8
65°	0.8



TEST NUMBER: P495609

CATALOG NUMBER: LDA2B109024R60D010 2LBDL1LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)