

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222790

Luminaire Tested: **LD2B05D010 EU2B05NFL259030 2LBDSQC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P222790  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B05D010 EU2B05NFL259030 2LBDSQC\*MW  
Description: 500 Lumen, 2inch Portfolio LED Downlight  
NARROW FLOOD OPTIC  
SQUARE CAST TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 588.0 lumens  
Efficiency: N/A  
Efficacy: 80.6 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P222790

CATALOG NUMBER: LD2B05D010 EU2B05NFL259030 2LBDSQC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P222790

CATALOG NUMBER: LD2B05D010 EU2B05NFL259030 2LBDSQC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	95
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	93	92
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	91	90
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	89	88	86
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	87	86	84
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	85	84	82
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84	83	82	80
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	81	80	79
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	79	79	79
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79	79	79	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1351218
5°	1247586
10°	844461
15°	287284
20°	105524
25°	55945
30°	28759
35°	13429
40°	4399
45°	2246
50°	1024
55°	405
60°	465
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222790

CATALOG NUMBER: LD2B05D010 EU2B05NFL259030 2LBDSQC\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	272.9	46.4
10°-20°	229.5	39.0
20°-30°	63.0	10.7
30°-40°	18.4	3.1
40°-50°	3.4	0.6
50°-60°	0.8	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	565.4	96.2
0°-40°	583.8	99.3
0°-60°	588.0	100.0
0°-90°	588.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	588.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3488	
5°	3209	273
15°	716	229
25°	131	63
35°	28	18
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222790

CATALOG NUMBER: LD2B05D010 EU2B05NFL259030 2LBDSQC\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3488.4
1°	3468.1
2°	3432.2
3°	3380.7
4°	3310.0
5°	3208.6
6°	3070.2
7°	2897.0
8°	2685.6
9°	2436.0
10°	2147.0
11°	1830.2
12°	1500.6
13°	1186.2
14°	918.0
15°	716.4
17.5°	404.3
20°	256.0
22.5°	182.4
25°	130.9
27.5°	92.7
30°	64.3
32.5°	45.2
35°	28.4
37.5°	11.6
40°	8.7
42.5°	6.4
45°	4.1
47.5°	2.3
50°	1.7
52.5°	1.2
55°	0.6
57.5°	0.6
60°	0.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222790

CATALOG NUMBER: LD2B05D010 EU2B05NFL259030 2LBDSQC\*MW

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)