

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495617

Luminaire Tested: **LDA2B109024R60D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P495617
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109024R60D010 2LBDLC1MMS
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 748.1 lumens
Efficiency: N/A
Efficacy: 74.8 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P495617

CATALOG NUMBER: LDA2B109024R60D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P495617

CATALOG NUMBER: LDA2B109024R60D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54		61	57	54		61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	442792
5°	431261
10°	419364
15°	398602
20°	364157
25°	312737
30°	232716
35°	136598
40°	65112
45°	30421
50°	15120
55°	5333
60°	1184
65°	934
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P495617

CATALOG NUMBER: LDA2B109024R60D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.9	11.0
10°-20°	217.1	29.0
20°-30°	257.8	34.5
30°-40°	145.5	19.5
40°-50°	37.9	5.1
50°-60°	6.9	0.9
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	556.9	74.4
0°-40°	702.4	93.9
0°-60°	747.2	99.9
0°-90°	748.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	748.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	898	
5°	871	82
15°	780	217
25°	574	258
35°	227	146
45°	44	38
55°	6	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495617

CATALOG NUMBER: LDA2B109024R60D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	897.5
1°	897.9
2°	891.7
3°	886.4
4°	876.1
5°	870.8
6°	861.3
7°	854.3
8°	847.7
9°	843.2
10°	837.1
11°	825.1
12°	814.1
13°	807.9
14°	793.5
15°	780.4
16°	765.2
17°	747.1
18°	729.8
19°	709.3
20°	693.6
21°	672.3
22.5°	636.9
23°	630.8
24°	600.8
25°	574.5
26°	545.3
27°	511.6
28°	478.3
29°	445.9
30°	408.5
32.5°	314.4
35°	226.8
37.5°	154.9
40°	101.1
42.5°	66.2
45°	43.6
47.5°	29.6
50°	19.7
52.5°	12.3
55°	6.2
57.5°	2.5
60°	1.2
62.5°	0.8
65°	0.8



TEST NUMBER: P495617

CATALOG NUMBER: LDA2B109024R60D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)