

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495638

Luminaire Tested: **LDA2B109024R65D010 2LBDL1WMH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495638  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109024R65D010 2LBDL1WMH  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 709.6 lumens  
Efficiency: N/A  
Efficacy: 71.0 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495638

CATALOG NUMBER: LDA2B109024R65D010 2LBDL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P495638

CATALOG NUMBER: LDA2B109024R65D010 2LBDL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	95	90	86	100	94	89	86	91	88	84		89	86	83		87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72		79	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58		66	61	57		65	60	57	56
9	74	64	58	54	73	64	58	54	63	57	54		62	57	54		61	57	53	52
10	71	61	55	51	69	60	54	51	59	54	50		59	54	50		58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	371205
5°	355735
10°	338758
15°	321987
20°	299527
25°	276483
30°	239894
35°	172133
40°	93514
45°	39910
50°	17193
55°	6193
60°	1085
65°	934
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P495638

CATALOG NUMBER: LDA2B109024R65D010 2LBDL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.2	9.5
10°-20°	176.6	24.9
20°-30°	230.9	32.5
30°-40°	175.6	24.8
40°-50°	50.8	7.2
50°-60°	7.7	1.1
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	474.7	66.9
0°-40°	650.3	91.6
0°-60°	708.8	99.9
0°-90°	709.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	709.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	752	
5°	718	67
15°	630	177
25°	508	231
35°	286	176
45°	57	51
55°	7	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495638

CATALOG NUMBER: LDA2B109024R65D010 2LBDL1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	752.4
1°	749.8
2°	745.6
3°	737.3
4°	728.2
5°	718.3
6°	708.8
7°	700.5
8°	692.5
9°	685.3
10°	676.2
11°	668.3
12°	659.9
13°	651.6
14°	642.5
15°	630.4
16°	621.3
17°	610.3
18°	593.6
19°	584.9
20°	570.5
21°	557.6
22.5°	537.9
23°	530.3
24°	518.6
25°	507.9
26°	493.9
27°	478.4
28°	461.3
29°	443.1
30°	421.1
32.5°	360.9
35°	285.8
37.5°	210.8
40°	145.2
42.5°	92.1
45°	57.2
47.5°	35.6
50°	22.4
52.5°	13.3
55°	7.2
57.5°	2.7
60°	1.1
62.5°	0.8
65°	0.8



TEST NUMBER: P495638

CATALOG NUMBER: LDA2B109024R65D010 2LBDL1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)