

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495663

Luminaire Tested: **LDA2B109024R70D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P495663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109024R70D010 2LBDLC1MMS
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 743.3 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P495663

CATALOG NUMBER: LDA2B109024R70D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P495663

CATALOG NUMBER: LDA2B109024R70D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	47	66	57	50	46	56	50	46		55	50	46		54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	294290
5°	292592
10°	290614
15°	285212
20°	274903
25°	263200
30°	250718
35°	206884
40°	134475
45°	70260
50°	32697
55°	11956
60°	1184
65°	934
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P495663

CATALOG NUMBER: LDA2B109024R70D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.9	7.5
10°-20°	156.9	21.1
20°-30°	222.7	30.0
30°-40°	208.3	28.0
40°-50°	83.8	11.3
50°-60°	14.6	2.0
60°-70°	0.7	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	435.5	58.6
0°-40°	643.8	86.6
0°-60°	742.2	99.9
0°-90°	743.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	743.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	596	
5°	591	56
15°	558	157
25°	484	223
35°	344	208
45°	101	84
55°	14	15
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495663

CATALOG NUMBER: LDA2B109024R70D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	596.5
1°	597.3
2°	596.1
3°	593.6
4°	592.4
5°	590.8
6°	584.2
7°	586.3
8°	580.5
9°	579.3
10°	580.1
11°	574.8
12°	573.6
13°	567.0
14°	564.6
15°	558.4
16°	554.7
17°	547.4
18°	538.8
19°	533.9
20°	523.6
21°	515.8
22.5°	501.5
23°	497.8
24°	490.9
25°	483.5
26°	477.8
27°	469.6
28°	461.4
29°	451.6
30°	440.1
32.5°	400.0
35°	343.5
37.5°	276.8
40°	208.8
42.5°	149.0
45°	100.7
47.5°	66.3
50°	42.6
52.5°	26.6
55°	13.9
57.5°	4.5
60°	1.2
62.5°	0.8
65°	0.8



TEST NUMBER: P495663

CATALOG NUMBER: LDA2B109024R70D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)