

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495754

Luminaire Tested: **LDA2B109027R35D010 2LBD1LI**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495754  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/12/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109027R35D010 2LBD1LI  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 833.3 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495754  
CATALOG NUMBER: LDA2B109027R35D010 2LBD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P495754

CATALOG NUMBER: LDA2B109027R35D010 2LBD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100	99	98	96
2	111	107	104	101	109	106	103	100	102	100	98		100	98	96		97	95	94	93
3	107	102	99	96	105	101	98	95	99	96	93		96	94	92		94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81	78	76	75
9	89	82	77	75	88	81	77	74	80	77	74		80	76	74		79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77	74	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1309580
5°	1259758
10°	1140915
15°	794190
20°	389201
25°	145182
30°	63748
35°	31018
40°	14233
45°	7675
50°	3761
55°	1032
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P495754

CATALOG NUMBER: LDA2B109027R35D010 2LBD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	235.0	28.2
10°-20°	412.0	49.4
20°-30°	140.4	16.8
30°-40°	34.9	4.2
40°-50°	9.0	1.1
50°-60°	1.7	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.4	94.5
0°-40°	822.3	98.7
0°-60°	833.0	100.0
0°-90°	833.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	833.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2654	
5°	2544	235
15°	1555	412
25°	267	140
35°	52	35
45°	11	9
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495754

CATALOG NUMBER: LDA2B109027R35D010 2LBD1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2654.4
1°	2649.1
2°	2628.7
3°	2609.1
4°	2577.6
5°	2543.7
6°	2510.7
7°	2479.6
8°	2412.6
9°	2347.7
10°	2277.4
11°	2162.3
12°	2037.3
13°	1876.4
14°	1727.3
15°	1554.9
16°	1386.6
17°	1211.4
18°	1047.6
19°	881.8
20°	741.3
21°	607.3
22.5°	445.6
23°	400.3
24°	326.7
25°	266.7
26°	220.6
27°	184.2
28°	155.2
29°	131.1
30°	111.9
32.5°	76.0
35°	51.5
37.5°	34.7
40°	22.1
42.5°	15.1
45°	11.0
47.5°	7.8
50°	4.9
52.5°	2.9
55°	1.2
57.5°	0.8
60°	0.4
62.5°	0.4
65°	0.4



TEST NUMBER: P495754

CATALOG NUMBER: LDA2B109027R35D010 2LBD1LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)