

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225338

Luminaire Tested: **LD2B05D010 EU2B05FL408035 2LBDC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225338  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B05D010 EU2B05FL408035 2LBDC\*MW  
Description: 500 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
CAST ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 677.0 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225338

CATALOG NUMBER: LD2B05D010 EU2B05FL408035 2LBDC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P225338

CATALOG NUMBER: LD2B05D010 EU2B05FL408035 2LBDC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86		
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82		
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79		
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75		
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72		
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69		
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66		
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	612898
5°	601746
10°	534917
15°	420700
20°	279928
25°	160698
30°	81179
35°	38207
40°	15372
45°	7614
50°	4158
55°	2904
60°	2711
65°	1558
70°	1925
75°	1347
80°	2008
85°	0



TEST NUMBER: P225338

CATALOG NUMBER: LD2B05D010 EU2B05FL408035 2LBDC\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.7	20.9
10°-20°	284.2	42.0
20°-30°	176.8	26.1
30°-40°	54.3	8.0
40°-50°	11.9	1.8
50°-60°	4.2	0.6
60°-70°	2.1	0.3
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	602.7	89.0
0°-40°	657.0	97.1
0°-60°	673.2	99.4
0°-90°	677.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	677.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1582	
5°	1548	142
15°	1049	284
25°	376	177
35°	81	54
45°	14	12
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P225338

CATALOG NUMBER: LD2B05D010 EU2B05FL408035 2LBDC\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1582.3
2.5°	1575.3
5°	1547.6
7.5°	1477.2
10°	1360.0
12.5°	1219.3
15°	1049.1
17.5°	863.2
20°	679.1
22.5°	515.0
25°	376.0
27.5°	264.9
30°	181.5
32.5°	122.4
35°	80.8
37.5°	48.6
40°	30.4
42.5°	20.8
45°	13.9
47.5°	9.6
50°	6.9
52.5°	6.1
55°	4.3
57.5°	3.5
60°	3.5
62.5°	2.6
65°	1.7
67.5°	1.7
70°	1.7
72.5°	1.7
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)