

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495819

Luminaire Tested: **LDA2B109027R60D010 2LBD1WH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495819  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109027R60D010 2LBD1WH  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 806.1 lumens  
Efficiency: N/A  
Efficacy: 80.6 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495819

CATALOG NUMBER: LDA2B109027R60D010 2LBD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P495819

CATALOG NUMBER: LDA2B109027R60D010 2LBD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65		73	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	482607
5°	458152
10°	448521
15°	434151
20°	396919
25°	352422
30°	263650
35°	148824
40°	56031
45°	25048
50°	12204
55°	2494
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P495819

CATALOG NUMBER: LDA2B109027R60D010 2LBD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.6	10.9
10°-20°	236.1	29.3
20°-30°	288.4	35.8
30°-40°	157.3	19.5
40°-50°	31.5	3.9
50°-60°	4.5	0.6
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	612.1	75.9
0°-40°	769.4	95.5
0°-60°	805.4	99.9
0°-90°	806.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	806.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	978	
5°	925	88
15°	850	236
25°	647	288
35°	247	157
45°	36	31
55°	3	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495819

CATALOG NUMBER: LDA2B109027R60D010 2LBD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	978.2
1°	973.7
2°	965.1
3°	953.7
4°	937.4
5°	925.1
6°	918.6
7°	910.8
8°	904.7
9°	901.8
10°	895.3
11°	887.9
12°	881.4
13°	873.6
14°	862.2
15°	850.0
16°	834.4
17°	812.8
18°	798.9
19°	776.4
20°	756.0
21°	737.2
22.5°	705.8
23°	692.7
24°	672.7
25°	647.4
26°	615.1
27°	581.2
28°	542.4
29°	505.6
30°	462.8
32.5°	354.9
35°	247.1
37.5°	154.8
40°	87.0
42.5°	54.3
45°	35.9
47.5°	24.5
50°	15.9
52.5°	8.2
55°	2.9
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.4



TEST NUMBER: P495819

CATALOG NUMBER: LDA2B109027R60D010 2LBD1WH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)