

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279576

Luminaire Tested: **LDA2B109040D010 EU2B10FL409040 2LBAD1WHH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279576
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B109040D010 EU2B10FL409040 2LBAD1WHH
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, WHH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 994.7 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279576

CATALOG NUMBER: LDA2B109040D010 EU2B10FL409040 2LBAD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P279576

CATALOG NUMBER: LDA2B109040D010 EU2B10FL409040 2LBAD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																												
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																												
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																												
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																												
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																												
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																												
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																												
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																												
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																												
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1367698
5°	1338750
10°	1220219
15°	953191
20°	564349
25°	209798
30°	65571
35°	29151
40°	13525
45°	6349
50°	3531
55°	1978
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P279576

CATALOG NUMBER: LDA2B109040D010 EU2B10FL409040 2LBAD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.9	25.1
10°-20°	496.9	50.0
20°-30°	203.5	20.5
30°-40°	33.7	3.4
40°-50°	8.0	0.8
50°-60°	2.1	0.2
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	950.3	95.5
0°-40°	984.0	98.9
0°-60°	994.1	99.9
0°-90°	994.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	994.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2772	
5°	2703	250
15°	1866	497
25°	385	204
35°	48	34
45°	9	8
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279576

CATALOG NUMBER: LDA2B109040D010 EU2B10FL409040 2LBAD1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2772.2
1°	2762.6
2°	2749.8
3°	2738.4
4°	2723.3
5°	2703.2
6°	2673.6
7°	2634.7
8°	2579.5
9°	2512.4
10°	2435.7
11°	2346.6
12°	2246.2
13°	2131.5
14°	2004.1
15°	1866.2
17.5°	1479.9
20°	1074.9
22.5°	688.1
25°	385.4
27.5°	203.2
30°	115.1
32.5°	73.1
35°	48.4
37.5°	32.0
40°	21.0
42.5°	13.7
45°	9.1
47.5°	6.4
50°	4.6
52.5°	3.2
55°	2.3
57.5°	1.4
60°	0.9
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279576

CATALOG NUMBER: LDA2B109040D010 EU2B10FL409040 2LBAD1WHH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)