

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280478

Luminaire Tested: **LDA2B109040D010 EU2B10WFL559040 2LBALD1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280478
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B109040D010 EU2B10WFL559040 2LBALD1WMH
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, WMH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 979.4 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280478

CATALOG NUMBER: LDA2B109040D010 EU2B10WFL559040 2LBALD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P280478

CATALOG NUMBER: LDA2B109040D010 EU2B10WFL559040 2LBALD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95																			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90																			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85																			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80																			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76																			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72																			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69																			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65																			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62																			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	836446
5°	819385
10°	761979
15°	665272
20°	550803
25°	421284
30°	230552
35°	85344
40°	29561
45°	13326
50°	6294
55°	3097
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P280478

CATALOG NUMBER: LDA2B109040D010 EU2B10WFL559040 2LBALD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.7	15.7
10°-20°	360.0	36.8
20°-30°	340.3	34.7
30°-40°	104.7	10.7
40°-50°	16.6	1.7
50°-60°	3.5	0.4
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	854.0	87.2
0°-40°	958.8	97.9
0°-60°	978.8	99.9
0°-90°	979.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	979.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1695	
5°	1654	154
15°	1302	360
25°	774	340
35°	142	105
45°	19	17
55°	4	3
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280478

CATALOG NUMBER: LDA2B109040D010 EU2B10WFL559040 2LBALD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1695.4
1°	1689.0
2°	1681.3
3°	1674.9
4°	1666.7
5°	1654.5
6°	1638.6
7°	1617.2
8°	1588.6
9°	1555.5
10°	1521.0
11°	1482.8
12°	1442.4
13°	1398.3
14°	1352.5
15°	1302.5
17.5°	1170.4
20°	1049.1
22.5°	926.0
25°	773.9
27.5°	590.4
30°	404.7
32.5°	248.4
35°	141.7
37.5°	79.0
40°	45.9
42.5°	28.6
45°	19.1
47.5°	12.7
50°	8.2
52.5°	5.4
55°	3.6
57.5°	2.3
60°	0.9
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280478

CATALOG NUMBER: LDA2B109040D010 EU2B10WFL559040 2LBALD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)