

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315012

Luminaire Tested: **LDA2B10NFL9040D010 PINW1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P315012
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B10NFL9040D010 PINW1MMS
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in Adj PinHole, White oculus, matte metallic silver finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 848.5 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P315012

CATALOG NUMBER: LDA2B10NFL9040D010 PINW1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P315012

CATALOG NUMBER: LDA2B10NFL9040D010 PINW1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2171877
5°	2002974
10°	1349771
15°	665477
20°	284248
25°	111758
30°	43980
35°	19273
40°	9274
45°	4465
50°	2456
55°	1376
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P315012

CATALOG NUMBER: LDA2B10NFL9040D010 PINW1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	342.6	40.4
10°-20°	369.0	43.5
20°-30°	106.5	12.6
30°-40°	22.5	2.6
40°-50°	5.5	0.7
50°-60°	1.6	0.2
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	818.1	96.4
0°-40°	840.6	99.1
0°-60°	847.7	99.9
0°-90°	848.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	848.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4402	
5°	4044	343
15°	1303	369
25°	205	107
35°	32	22
45°	6	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315012

CATALOG NUMBER: LDA2B10NFL9040D010 PINW1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	4402.2
1°	4374.5
2°	4327.7
3°	4264.5
4°	4174.9
5°	4044.4
6°	3868.3
7°	3638.7
8°	3356.1
9°	3026.8
10°	2694.3
11°	2358.1
12°	2040.8
13°	1759.1
14°	1511.4
15°	1302.9
17.5°	861.1
20°	541.4
22.5°	332.9
25°	205.3
27.5°	125.3
30°	77.2
32.5°	48.8
35°	32.0
37.5°	21.2
40°	14.4
42.5°	10.0
45°	6.4
47.5°	4.0
50°	3.2
52.5°	2.4
55°	1.6
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P315012

CATALOG NUMBER: LDA2B10NFL9040D010 PINW1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)