

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264747

Luminaire Tested: **LD2B05D010 EU2B0510SP158040 2LBDL*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264747
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B0510SP158040 2LBDL*GPH
Description: 500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 725.1 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264747

CATALOG NUMBER: LD2B05D010 EU2B0510SP158040 2LBDL*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P264747

CATALOG NUMBER: LD2B05D010 EU2B0510SP158040 2LBDL*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97				97															
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94				94															
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92				92															
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89				89															
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87				87															
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85				85															
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83				83															
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81				81															
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79				79															
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78				78															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2559413
5°	2083105
10°	1125235
15°	448657
20°	179926
25°	86173
30°	44663
35°	23610
40°	13074
45°	8094
50°	5603
55°	3785
60°	2861
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264747

CATALOG NUMBER: LD2B05D010 EU2B0510SP158040 2LBDL*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	338.3	46.7
10°-20°	266.9	36.8
20°-30°	78.7	10.9
30°-40°	26.2	3.6
40°-50°	9.9	1.4
50°-60°	4.4	0.6
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	683.9	94.3
0°-40°	710.1	97.9
0°-60°	724.4	99.9
0°-90°	725.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	725.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5188	
5°	4206	338
15°	878	267
25°	158	79
35°	39	26
45°	12	10
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264747

CATALOG NUMBER: LD2B05D010 EU2B0510SP158040 2LBDL*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5187.7
2.5°	4978.6
5°	4206.2
7.5°	3240.7
10°	2246.1
12.5°	1437.4
15°	878.4
17.5°	535.8
20°	342.7
22.5°	229.4
25°	158.3
27.5°	111.8
30°	78.4
32.5°	55.2
35°	39.2
37.5°	27.6
40°	20.3
42.5°	16.0
45°	11.6
47.5°	10.2
50°	7.3
52.5°	5.8
55°	4.4
57.5°	4.4
60°	2.9
62.5°	1.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)