

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264752

Luminaire Tested: **LD2B05D010 EU2B0510SP158040 2LBLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264752
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B0510SP158040 2LBLC*MW
Description: 500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 797.0 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264752

CATALOG NUMBER: LD2B05D010 EU2B0510SP158040 2LBLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P264752

CATALOG NUMBER: LD2B05D010 EU2B0510SP158040 2LBLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97						97													
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94						94													
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92						92													
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89						89													
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87						87													
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85						85													
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83						83													
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81						81													
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79						79													
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78						78													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2813593
5°	2289970
10°	1237002
15°	493195
20°	197777
25°	94719
30°	49107
35°	25958
40°	14362
45°	8931
50°	6140
55°	4129
60°	3158
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264752

CATALOG NUMBER: LD2B05D010 EU2B0510SP158040 2LBLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	371.9	46.7
10°-20°	293.4	36.8
20°-30°	86.6	10.9
30°-40°	28.8	3.6
40°-50°	10.8	1.4
50°-60°	4.8	0.6
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	751.8	94.3
0°-40°	780.6	97.9
0°-60°	796.3	99.9
0°-90°	797.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	797.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5703	
5°	4624	372
15°	966	293
25°	174	87
35°	43	29
45°	13	11
55°	5	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264752

CATALOG NUMBER: LD2B05D010 EU2B0510SP158040 2LBLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5702.9
2.5°	5473.0
5°	4623.9
7.5°	3562.5
10°	2469.2
12.5°	1580.1
15°	965.6
17.5°	589.0
20°	376.7
22.5°	252.2
25°	174.0
27.5°	122.9
30°	86.2
32.5°	60.7
35°	43.1
37.5°	30.3
40°	22.3
42.5°	17.6
45°	12.8
47.5°	11.2
50°	8.0
52.5°	6.4
55°	4.8
57.5°	4.8
60°	3.2
62.5°	1.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)