

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225118

Luminaire Tested: **LD2B05D010 EU2B05FL408040 2LBD*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225118
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B05FL408040 2LBD*GPH
Description: 500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 816.0 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225118

CATALOG NUMBER: LD2B05D010 EU2B05FL408040 2LBD*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P225118

CATALOG NUMBER: LD2B05D010 EU2B05FL408040 2LBD*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	106	102	100	108	104	101	98	101	99	96	98	96	94	95	94	92	91				91
3	106	100	96	93	104	99	95	92	96	93	91	94	92	89	92	90	88	87				87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83				83
5	98	91	86	83	96	90	85	82	88	84	81	87	83	81	85	82	80	79				79
6	94	87	82	78	93	86	81	78	85	81	78	83	80	77	82	79	77	75				75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72				72
8	87	80	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	69				69
9	84	76	72	68	83	76	71	68	75	71	68	74	70	68	73	70	68	66				66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64				64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	740257
5°	725276
10°	644457
15°	505634
20°	340069
25°	197838
30°	99115
35°	46246
40°	21591
45°	9093
50°	4399
55°	2836
60°	1627
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225118

CATALOG NUMBER: LD2B05D010 EU2B05FL408040 2LBD*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.7	20.9
10°-20°	342.3	41.9
20°-30°	216.4	26.5
30°-40°	67.3	8.3
40°-50°	14.9	1.8
50°-60°	3.8	0.5
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	729.4	89.4
0°-40°	796.7	97.6
0°-60°	815.5	99.9
0°-90°	816.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	816.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1911	
5°	1865	171
15°	1261	342
25°	463	216
35°	98	67
45°	17	15
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225118

CATALOG NUMBER: LD2B05D010 EU2B05FL408040 2LBD*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1911.1
2.5°	1902.7
5°	1865.3
7.5°	1776.9
10°	1638.5
12.5°	1463.7
15°	1260.9
17.5°	1041.4
20°	825.0
22.5°	630.4
25°	462.9
27.5°	324.6
30°	221.6
32.5°	146.7
35°	97.8
37.5°	65.5
40°	42.7
42.5°	26.0
45°	16.6
47.5°	11.4
50°	7.3
52.5°	5.2
55°	4.2
57.5°	3.1
60°	2.1
62.5°	1.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)