

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495919

Luminaire Tested: **LDA2B109030R20D010 2LBDLC1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495919  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109030R20D010 2LBDLC1MB  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 873.9 lumens  
Efficiency: N/A  
Efficacy: 87.4 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.34  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495919

CATALOG NUMBER: LDA2B109030R20D010 2LBDLC1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P495919

CATALOG NUMBER: LDA2B109030R20D010 2LBDLC1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	102	104	102	100	101	100	98	98	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	97	95	94	92
4	106	101	98	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	92	102	97	94	91	96	93	90	94	92	90	93	91	89	88
6	101	95	91	89	100	95	91	88	93	90	88	92	89	87	91	89	87	86
7	98	93	89	86	97	92	89	86	91	88	86	90	87	85	89	87	85	84
8	96	90	87	84	95	90	86	84	89	86	84	88	85	83	87	85	83	82
9	94	88	85	82	93	88	84	82	87	84	82	86	84	82	86	83	81	81
10	92	86	83	80	91	86	83	80	85	82	80	85	82	80	84	82	80	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2889077
5°	2441961
10°	1487889
15°	612153
20°	220405
25°	88405
30°	40163
35°	18912
40°	9983
45°	5372
50°	3147
55°	1548
60°	888
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P495919

CATALOG NUMBER: LDA2B109030R20D010 2LBDLC1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	406.7	46.5
10°-20°	351.8	40.3
20°-30°	84.8	9.7
30°-40°	21.7	2.5
40°-50°	6.5	0.7
50°-60°	1.9	0.2
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	843.3	96.5
0°-40°	865.1	99.0
0°-60°	873.5	99.9
0°-90°	873.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	873.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5856	
5°	4931	407
15°	1198	352
25°	162	85
35°	31	22
45°	8	7
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495919

CATALOG NUMBER: LDA2B109030R20D010 2LBDLC1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5855.9
1°	5805.0
2°	5683.5
3°	5498.9
4°	5261.0
5°	4930.8
6°	4589.7
7°	4213.1
8°	3821.9
9°	3383.0
10°	2970.0
11°	2538.4
12°	2160.0
13°	1802.0
14°	1473.6
15°	1198.5
16°	971.1
17°	784.1
18°	632.7
19°	520.3
20°	419.8
22.5°	258.8
25°	162.4
27.5°	105.5
30°	70.5
32.5°	46.4
35°	31.4
37.5°	21.8
40°	15.5
42.5°	10.9
45°	7.7
47.5°	5.9
50°	4.1
52.5°	2.7
55°	1.8
57.5°	1.4
60°	0.9
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0



TEST NUMBER: P495919

CATALOG NUMBER: LDA2B109030R20D010 2LBDLC1MB

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)