

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224937

Luminaire Tested: **LD2B05D010 EU2B05FL408040 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224937
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B05FL408040 2LBD*H
Description: 500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 806.0 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224937

CATALOG NUMBER: LD2B05D010 EU2B05FL408040 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224937

CATALOG NUMBER: LD2B05D010 EU2B05FL408040 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95																
2	110	106	103	100	108	104	101	99	101	99	97	98	96	94	96	94	93	91			91																
3	106	100	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87			87																
4	102	96	91	88	100	94	90	87	92	89	86	91	88	85	89	86	84	83			83																
5	98	91	86	83	96	90	86	82	89	85	82	87	84	81	86	83	80	79			79																
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76			76																
7	91	83	78	75	90	83	78	75	82	77	74	80	77	74	79	76	74	73			73																
8	88	80	75	72	87	79	75	72	78	74	71	77	74	71	77	73	71	70			70																
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67			67																
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64			64																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	747578
5°	731925
10°	644614
15°	505754
20°	335865
25°	192795
30°	96699
35°	44638
40°	18153
45°	8107
50°	4218
55°	2634
60°	1240
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224937

CATALOG NUMBER: LD2B05D010 EU2B05FL408040 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.9	21.3
10°-20°	341.4	42.4
20°-30°	212.1	26.3
30°-40°	64.0	7.9
40°-50°	13.1	1.6
50°-60°	3.4	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	725.4	90.0
0°-40°	789.4	97.9
0°-60°	805.8	100.0
0°-90°	806.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	806.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1930	
5°	1882	172
15°	1261	341
25°	451	212
35°	94	64
45°	15	13
55°	4	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224937

CATALOG NUMBER: LD2B05D010 EU2B05FL408040 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1930.0
1°	1923.8
2°	1915.2
3°	1909.0
4°	1899.6
5°	1882.4
6°	1855.1
7°	1817.7
8°	1763.8
9°	1702.9
10°	1638.9
11°	1571.0
12°	1500.0
13°	1425.9
14°	1344.7
15°	1261.2
17.5°	1037.2
20°	814.8
22.5°	618.1
25°	451.1
27.5°	318.4
30°	216.2
32.5°	142.0
35°	94.4
37.5°	58.5
40°	35.9
42.5°	23.4
45°	14.8
47.5°	9.4
50°	7.0
52.5°	4.7
55°	3.9
57.5°	2.3
60°	1.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224937

CATALOG NUMBER: LD2B05D010 EU2B05FL408040 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)