

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280482

Luminaire Tested: **LDA2B109050D010 EU2B10WFL559050 2LBAD1H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280482  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B109050D010 EU2B10WFL559050 2LBAD1H  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl, Self-Flanged, H  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1012.5 lumens  
Efficiency: N/A  
Efficacy: 101.3 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280482

CATALOG NUMBER: LDA2B109050D010 EU2B10WFL559050 2LBAD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P280482

CATALOG NUMBER: LDA2B109050D010 EU2B10WFL559050 2LBAD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	864715
5°	847119
10°	787729
15°	687797
20°	569442
25°	435546
30°	238299
35°	88235
40°	30527
45°	13745
50°	6524
55°	3269
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P280482

CATALOG NUMBER: LDA2B109050D010 EU2B10WFL559050 2LBAD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.9	15.7
10°-20°	372.2	36.8
20°-30°	351.8	34.7
30°-40°	108.3	10.7
40°-50°	17.1	1.7
50°-60°	3.6	0.4
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	882.9	87.2
0°-40°	991.2	97.9
0°-60°	1011.9	99.9
0°-90°	1012.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1012.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1753	
5°	1710	159
15°	1347	372
25°	800	352
35°	146	108
45°	20	17
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280482

CATALOG NUMBER: LDA2B109050D010 EU2B10WFL559050 2LBAD1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1752.7
1°	1746.2
2°	1738.2
3°	1731.6
4°	1723.2
5°	1710.5
6°	1694.1
7°	1672.0
8°	1642.4
9°	1608.1
10°	1572.4
11°	1533.0
12°	1491.2
13°	1445.7
14°	1398.3
15°	1346.6
17.5°	1210.0
20°	1084.6
22.5°	957.4
25°	800.1
27.5°	610.4
30°	418.3
32.5°	256.8
35°	146.5
37.5°	81.7
40°	47.4
42.5°	29.6
45°	19.7
47.5°	13.1
50°	8.5
52.5°	5.6
55°	3.8
57.5°	2.3
60°	0.9
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280482

CATALOG NUMBER: LDA2B109050D010 EU2B10WFL559050 2LBAD1H

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)