

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B05D010 EU2B05WFL558040 2LBDSQLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14811)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B05WFL558040 2LBDSQLC*MMS
Description: 500 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 673.0 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B05WFL558040 2LBDSQLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B05WFL558040 2LBDSQLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 93 | | | |
| 2 | 108 | 103 | 99 | 95 | 106 | 101 | 97 | 94 | 98 | 95 | 92 | 95 | 92 | 90 | 92 | 90 | 88 | 87 | | | |
| 3 | 102 | 96 | 91 | 87 | 100 | 94 | 90 | 86 | 92 | 88 | 84 | 89 | 86 | 83 | 87 | 84 | 82 | 80 | | | |
| 4 | 97 | 89 | 84 | 79 | 95 | 88 | 83 | 79 | 86 | 81 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 75 | | | |
| 5 | 92 | 83 | 77 | 73 | 90 | 82 | 77 | 73 | 81 | 76 | 72 | 79 | 75 | 71 | 77 | 74 | 71 | 69 | | | |
| 6 | 87 | 78 | 72 | 68 | 86 | 77 | 72 | 67 | 76 | 71 | 67 | 74 | 70 | 66 | 73 | 69 | 66 | 65 | | | |
| 7 | 83 | 73 | 67 | 63 | 81 | 73 | 67 | 63 | 71 | 66 | 62 | 70 | 65 | 62 | 69 | 65 | 62 | 60 | | | |
| 8 | 79 | 69 | 63 | 59 | 77 | 68 | 63 | 59 | 67 | 62 | 58 | 66 | 62 | 58 | 65 | 61 | 58 | 56 | | | |
| 9 | 75 | 65 | 59 | 55 | 74 | 65 | 59 | 55 | 64 | 58 | 55 | 63 | 58 | 55 | 62 | 58 | 54 | 53 | | | |
| 10 | 71 | 62 | 56 | 52 | 70 | 61 | 55 | 52 | 60 | 55 | 51 | 59 | 55 | 51 | 59 | 54 | 51 | 50 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 321303 |
| 5° | 318215 |
| 10° | 295384 |
| 15° | 259293 |
| 20° | 223127 |
| 25° | 189889 |
| 30° | 150372 |
| 35° | 104408 |
| 40° | 66341 |
| 45° | 39989 |
| 50° | 22839 |
| 55° | 12493 |
| 60° | 1394 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B05WFL558040 2LBDSQLC*MMS

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 75.9 | 11.3 |
| 10°-20° | 180.0 | 26.7 |
| 20°-30° | 202.0 | 30.0 |
| 30°-40° | 139.2 | 20.7 |
| 40°-50° | 58.9 | 8.7 |
| 50°-60° | 16.6 | 2.5 |
| 60°-70° | 0.4 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 457.9 | 68.0 |
| 0°-40° | 597.2 | 88.7 |
| 0°-60° | 672.6 | 99.9 |
| 0°-90° | 673.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 673.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 830 | |
| 5° | 818 | 76 |
| 15° | 647 | 180 |
| 25° | 444 | 202 |
| 35° | 221 | 139 |
| 45° | 73 | 59 |
| 55° | 18 | 17 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B05WFL558040 2LBDSQLC*MMS

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 829.5 |
| 2.5° | 826.7 |
| 5° | 818.4 |
| 7.5° | 792.5 |
| 10° | 751.0 |
| 12.5° | 700.2 |
| 15° | 646.6 |
| 17.5° | 590.2 |
| 20° | 541.3 |
| 22.5° | 494.2 |
| 25° | 444.3 |
| 27.5° | 392.6 |
| 30° | 336.2 |
| 32.5° | 275.3 |
| 35° | 220.8 |
| 37.5° | 172.7 |
| 40° | 131.2 |
| 42.5° | 98.8 |
| 45° | 73.0 |
| 47.5° | 52.7 |
| 50° | 37.9 |
| 52.5° | 27.7 |
| 55° | 18.5 |
| 57.5° | 9.2 |
| 60° | 1.8 |
| 62.5° | 0.9 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)