

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280491

Luminaire Tested: **LDA2B109050D010 EU2B10WFL559050 2LBALD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280491
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B109050D010 EU2B10WFL559050 2LBALD1H
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 999.0 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280491

CATALOG NUMBER: LDA2B109050D010 EU2B10WFL559050 2LBALD1H

Luminous Intensity Polar Plot





TEST NUMBER: P280491

CATALOG NUMBER: LDA2B109050D010 EU2B10WFL559050 2LBALD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	853220
5°	835827
10°	777259
15°	678603
20°	561829
25°	429721
30°	235166
35°	87030
40°	30141
45°	13606
50°	6371
55°	3183
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P280491

CATALOG NUMBER: LDA2B109050D010 EU2B10WFL559050 2LBALD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.8	15.7
10°-20°	367.2	36.8
20°-30°	347.1	34.7
30°-40°	106.8	10.7
40°-50°	16.9	1.7
50°-60°	3.6	0.4
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	871.1	87.2
0°-40°	978.0	97.9
0°-60°	998.4	99.9
0°-90°	999.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	999.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1729	
5°	1688	157
15°	1329	367
25°	789	347
35°	144	107
45°	20	17
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280491

CATALOG NUMBER: LDA2B109050D010 EU2B10WFL559050 2LBALD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1729.4
1°	1722.9
2°	1715.0
3°	1708.5
4°	1700.2
5°	1687.7
6°	1671.5
7°	1649.7
8°	1620.5
9°	1586.7
10°	1551.5
11°	1512.6
12°	1471.3
13°	1426.4
14°	1379.6
15°	1328.6
17.5°	1193.8
20°	1070.1
22.5°	944.6
25°	789.4
27.5°	602.2
30°	412.8
32.5°	253.4
35°	144.5
37.5°	80.6
40°	46.8
42.5°	29.2
45°	19.5
47.5°	13.0
50°	8.3
52.5°	5.6
55°	3.7
57.5°	2.3
60°	0.9
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280491

CATALOG NUMBER: LDA2B109050D010 EU2B10WFL559050 2LBALD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)