

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315015

Luminaire Tested: **LDA2B10NFL9050D010 PIN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P315015
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B10NFL9050D010 PIN1MW
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in Adj PinHole, Black oculus, matte white finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 862.4 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P315015

CATALOG NUMBER: LDA2B10NFL9050D010 PIN1MW

Luminous Intensity Polar Plot





TEST NUMBER: P315015

CATALOG NUMBER: LDA2B10NFL9050D010 PIN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97			97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94			94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91			91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89			89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86			86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84			84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82			82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80			80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78			78
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76			76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2207350
5°	2035710
10°	1371814
15°	676356
20°	288921
25°	113554
30°	44720
35°	19574
40°	9403
45°	4535
50°	2533
55°	1376
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P315015

CATALOG NUMBER: LDA2B10NFL9050D010 PIN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.2	40.4
10°-20°	375.0	43.5
20°-30°	108.3	12.6
30°-40°	22.9	2.6
40°-50°	5.6	0.7
50°-60°	1.6	0.2
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	831.5	96.4
0°-40°	854.3	99.1
0°-60°	861.6	99.9
0°-90°	862.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	862.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4474	
5°	4110	348
15°	1324	375
25°	209	108
35°	32	23
45°	6	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315015

CATALOG NUMBER: LDA2B10NFL9050D010 PIN1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4474.1
1°	4446.1
2°	4398.5
3°	4334.2
4°	4243.1
5°	4110.5
6°	3931.6
7°	3698.1
8°	3411.0
9°	3076.3
10°	2738.3
11°	2396.7
12°	2074.2
13°	1787.9
14°	1536.1
15°	1324.2
17.5°	875.2
20°	550.3
22.5°	338.4
25°	208.6
27.5°	127.3
30°	78.5
32.5°	49.6
35°	32.5
37.5°	21.6
40°	14.6
42.5°	10.2
45°	6.5
47.5°	4.1
50°	3.3
52.5°	2.4
55°	1.6
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P315015

CATALOG NUMBER: LDA2B10NFL9050D010 PIN1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)