

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278636

Luminaire Tested: **LDA2B109027D010 EU2B10NFL259027 2LBALD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278636
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B109027D010 EU2B10NFL259027 2LBALD1MW
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 817.2 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278636

CATALOG NUMBER: LDA2B109027D010 EU2B10NFL259027 2LBALD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P278636

CATALOG NUMBER: LDA2B109027D010 EU2B10NFL259027 2LBALD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97				97															
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94				94															
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91				91															
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89				89															
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86				86															
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84				84															
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82				82															
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80				80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78				78															
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76				76															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2091706
5°	1929084
10°	1299974
15°	640909
20°	273748
25°	107621
30°	42385
35°	18550
40°	8952
45°	4326
50°	2379
55°	1290
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P278636

CATALOG NUMBER: LDA2B109027D010 EU2B10NFL259027 2LBALD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.9	40.4
10°-20°	355.3	43.5
20°-30°	102.6	12.6
30°-40°	21.6	2.6
40°-50°	5.3	0.7
50°-60°	1.5	0.2
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.9	96.4
0°-40°	809.5	99.1
0°-60°	816.4	99.9
0°-90°	817.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	817.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4240	
5°	3895	330
15°	1255	355
25°	198	103
35°	31	22
45°	6	5
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278636

CATALOG NUMBER: LDA2B109027D010 EU2B10NFL259027 2LBALD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4239.7
1°	4213.1
2°	4168.0
3°	4107.1
4°	4020.8
5°	3895.2
6°	3725.6
7°	3504.4
8°	3232.3
9°	2915.1
10°	2594.9
11°	2271.1
12°	1965.5
13°	1694.2
14°	1455.6
15°	1254.8
17.5°	829.4
20°	521.4
22.5°	320.6
25°	197.7
27.5°	120.6
30°	74.4
32.5°	47.0
35°	30.8
37.5°	20.4
40°	13.9
42.5°	9.6
45°	6.2
47.5°	3.9
50°	3.1
52.5°	2.3
55°	1.5
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P278636

CATALOG NUMBER: LDA2B109027D010 EU2B10NFL259027 2LBALD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)