

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496199

Luminaire Tested: **LDA2B109035R35D010 2LBDC1MB**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496199  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/12/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109035R35D010 2LBDC1MB  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 902.5 lumens  
Efficiency: N/A  
Efficacy: 90.3 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496199

CATALOG NUMBER: LDA2B109035R35D010 2LBDC1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P496199

CATALOG NUMBER: LDA2B109035R35D010 2LBDC1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100	99	98	96
2	111	107	104	101	109	106	103	100	102	100	98		100	98	96		97	95	94	93
3	107	102	99	96	105	101	98	95	99	96	93		96	94	92		94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81	78	76	75
9	89	82	77	75	88	81	77	74	80	77	74		80	76	74		79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77	74	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1418415
5°	1364503
10°	1235749
15°	860181
20°	421542
25°	157267
30°	69046
35°	33547
40°	15393
45°	8303
50°	4068
55°	1118
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P496199

CATALOG NUMBER: LDA2B109035R35D010 2LBDC1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	254.6	28.2
10°-20°	446.2	49.4
20°-30°	152.1	16.8
30°-40°	37.8	4.2
40°-50°	9.7	1.1
50°-60°	1.8	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	852.8	94.5
0°-40°	890.6	98.7
0°-60°	902.2	100.0
0°-90°	902.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	902.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2875	
5°	2755	255
15°	1684	446
25°	289	152
35°	56	38
45°	12	10
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496199

CATALOG NUMBER: LDA2B109035R35D010 2LBDC1MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2875.0
1°	2869.3
2°	2847.2
3°	2825.9
4°	2791.9
5°	2755.2
6°	2719.3
7°	2685.7
8°	2613.2
9°	2542.8
10°	2466.7
11°	2342.0
12°	2206.6
13°	2032.3
14°	1870.8
15°	1684.1
16°	1501.9
17°	1312.1
18°	1134.7
19°	955.1
20°	802.9
21°	657.8
22.5°	482.6
23°	433.5
24°	353.9
25°	288.9
26°	238.9
27°	199.5
28°	168.1
29°	142.0
30°	121.2
32.5°	82.3
35°	55.7
37.5°	37.6
40°	23.9
42.5°	16.4
45°	11.9
47.5°	8.4
50°	5.3
52.5°	3.1
55°	1.3
57.5°	0.9
60°	0.4
62.5°	0.4
65°	0.4



TEST NUMBER: P496199

CATALOG NUMBER: LDA2B109035R35D010 2LBDC1MB

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)