

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496232

Luminaire Tested: **LDA2B109035R45D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496232  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109035R45D010 2LBDL1GPH  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 854.4 lumens  
Efficiency: N/A  
Efficacy: 85.4 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496232

CATALOG NUMBER: LDA2B109035R45D010 2LBDL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P496232

CATALOG NUMBER: LDA2B109035R45D010 2LBDL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80	86	82	80	84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66	73	69	66	72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63	70	66	63	69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	846806
5°	828151
10°	768342
15°	655261
20°	493313
25°	297386
30°	143390
35°	64986
40°	29948
45°	15420
50°	8136
55°	3011
60°	888
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P496232

CATALOG NUMBER: LDA2B109035R45D010 2LBDL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.5	18.2
10°-20°	350.3	41.0
20°-30°	250.3	29.3
30°-40°	75.0	8.8
40°-50°	18.6	2.2
50°-60°	3.9	0.5
60°-70°	0.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	756.1	88.5
0°-40°	831.1	97.3
0°-60°	853.6	99.9
0°-90°	854.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	854.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1716	
5°	1672	155
15°	1283	350
25°	546	250
35°	108	75
45°	22	19
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496232

CATALOG NUMBER: LDA2B109035R45D010 2LBDL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1716.4
1°	1719.5
2°	1715.6
3°	1701.0
4°	1690.3
5°	1672.2
6°	1654.1
7°	1634.6
8°	1602.8
9°	1572.7
10°	1533.7
11°	1494.8
12°	1445.7
13°	1393.1
14°	1344.0
15°	1282.9
16°	1223.2
17°	1155.5
18°	1091.4
19°	1012.6
20°	939.6
21°	858.7
22.5°	737.9
23°	697.2
24°	618.0
25°	546.3
26°	474.7
27°	409.2
28°	348.2
29°	298.2
30°	251.7
32.5°	165.5
35°	107.9
37.5°	70.8
40°	46.5
42.5°	31.4
45°	22.1
47.5°	15.9
50°	10.6
52.5°	6.6
55°	3.5
57.5°	1.8
60°	0.9
62.5°	0.9
65°	0.4



TEST NUMBER: P496232

CATALOG NUMBER: LDA2B109035R45D010 2LBDL1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)